



HP90 Fluorescent

Recessed Fluorescent Direct/Indirect – 2' x 4' with Acrylic Linear Prismatic Lens, Air Supply or Return with two 28 watt T5 Lamps

Recessed Fluorescent Direct/Indirect – 2' x 4' with Acrylic Linear Prismatic Lens, Air Supply or Return with two 28 watt T5 Lamps

HP90 Recessed Direct/Indirect: DayBrite's HP90, part of our popular soft light collection of luminaires, specifically addresses today's needs for balance brightness lighting, while exceeding LEED requirements for reducing energy consumption. The HP90 combines a recessed contoured body with an enclosed linear prismatic translucent lens to create an exciting 90.4% efficient direct/indirect luminaire. HP90 is available both in static and Air Supply or Return construction

Product data

General Information	
Lamp Envelope Code	T-5
Lamp Source Code	Fluorescent
Lamp Watts	28
Number of Lamps	2
Mounting	Recessed

Operating and Electrical	
Voltages	277 V

Mechanical and Housing	
Fixture Size	2 ft x 4 ft

Product Data	
Order product name	Recessed Fluorescent Direct/Indirect – 2' x 4' with Acrylic Linear Prismatic Lens, Air Supply or Return with two 28 watt T5 Lamps
Order code	H9A2GLR228UNVPG
Material Nr. (12NC)	CFI00001585
Catalog Number	H9A2GLR228UNVPG
Catalog Number Description	Recessed Fluorescent Direct/Indirect – 2' x 4' with Acrylic Linear Prismatic Lens, Air Supply or Return with two 28 watt T5 Lamps