



Incandescent Infrared Reflector Flood

Reflector Infrared BR40,PAR38

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. Philips Infrared lamps are suited for heating and drying in industrial and commercial applications. These incandescent, gas-filled infrared heat lamps come up to full temperature almost immediately, eliminating costly warm-up time. Highly efficient heat generators that produce a minimum of light rays and a high amount of infrared radiation. The BR40 lamp provides a built-in reflector for radiant energy control.

Benefits

- No warm-up time required.
- Decreased heat loss.

Features

- Instantaneous heat
- Radiated heat only warms object to be heated
- Build-in reflector for radiant energy control

Application

- Ideal for bathroom recessed fixtures and commercial and industrial applications.


Reflector Infrared BR40,PAR38

Versions



E26/E27, PAR38

Dimensional drawing



Product	D	C (max)	C1 (max)
175PAR38/HEAT/CL 120V 12/1	4-13/16 in	5-5/16 in	4-7/8 in

