



# Product Description

## Appliance Refrigerator Tubular

Tubular lamp with clear glass bulb

### Benefits

- Long useful life in refrigerators and freezers


### Features

- Reinforced filament
- T-CLICK design with integrated lampholder reduces integral costs of refrigerator lighting

### Application

- Refrigerators and freezers

### Dimensional drawing



Product	D (max)	C (max)
App 15W E14 230-240V T25CL RF 1CT/20F/NO	25 mm	57 mm
Appl 15W E14 230-240V T25 CL RF 1CT	25 mm	57 mm
Appl 15W E14 230-240V T25 CL RF 2BL/10	25 mm	57 mm