



LBD Low Bay

1 Lamp 250wHPS, Acrylic Lens

1 Lamp 250wHPS, Acrylic Lens

The LBD Low Bay Luminaire offers the highest efficiency for general purpose industrial lighting of any low bay manufactured in the U.S. It is the finest fixture made for mounting heights of 30' and below.

Product data

General Information	
Lamp Envelope Code	BT/ED/E-18
Lamp Source Code	High Pressure Sodium
Lamp Watts	250
Number of Lamps	1
Photometric Distribution Type	Direct
Mounting	Suspended

Operating and Electrical	
Voltages	120/208/240/277/347/480 V
Luminaire Input Watts	295

Mechanical and Housing	
Shape	Round

Product Data	
Order product name	1 Lamp 250wHPS, Acrylic Lens
Order code	LBD250S-BRA
Material Nr. (12NC)	DAY00003455
Catalog Number	LBD250S-BRA
Catalog Number Description	1 Lamp 250wHPS, Acrylic Lens