



# FBH/FBS145 C

## FBH145 C 2xPL-C/2P18W IC WH

2, MASTER PL-C 2 Pin, 18 W, White

Professional standard recessed downlights with a 145mm internal diameter. Complete with a very efficient highly polished reflector in silver aluminium finish. Suitable for incandescent, halogen, compact fluorescent and high intensity discharge lamps.

### Product data

General Information	
Lamp family code	PL-C/2P [MASTER PL-C 2 Pin]
Gear	CONV [Conventional]
Light Technical	
Number of light sources	2
Optical cover type	-
Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Power Consumption	18 W
Controls and Dimming	
Driver/power unit/transformer	-

Mechanical and Housing	
Housing Color	White
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Product Data	
Order product name	FBH145 C 2xPL-C/2P18W IC WH
Full product name	FBH145 C 2xPL-C/2P18W IC WH
Full product code	910403630230
Order code	910403630230
Material Nr. (12NC)	910403630230
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## FBH/FBS145 C

### Dimensional drawing

