

# Standard

## STANDARD MAG BALLAST (1) 13W COMPACT(2-PIN) 120V

Available for many fluorescent lamp types sold today, including Preheat, Rapid Start, 2-pin CFL, Slimline, High Output, Very High Output and Circline. Magnetic ballasts can be used in any application where these lamps are used.

### Product data


General Information		Rated Lamp Power	
Lamp Type	CFQ13W/GX23	Rated Lamp Power	13 W
Number of Lamps	1 piece/unit	<b>Wiring</b>	
Lamp Footage	-	Wire Striplength	0.50/0.375 mm
Ballast Type	Magnetic Fluorescent	Lamp Connection	Series
Base Model	LC13TP	Wire Length by Color	See data sheet
Suitable For Outdoor Use	Yes	Wire Gauge (Nom)	18AWG mm
Automatic Restart	Yes	Wire Type	Solid
<b>Operating and Electrical</b>		Remote Wiring Configuration Allowed	Yes
Input Voltage	120 V	Tandem Wiring Configuration Allowed	No
Input Frequency	60 Hz	Through Wiring Configuration Allowed	No
Total Harmonic Distortion USA	15 %	Max Ballast-Lamp Distance Remote Wiring	30'
Ignition Method	Preheat	Max Ballast-Lamp Distance Tandem Wiring	-
Crestfactor (Nom)	1.5	Max Ballast-Lamp Distance Through Wiring	-
Ignition Time (Nom)	1 s	<b>Mechanical and Housing</b>	
Input Current (Open Circuit)	0	Housing Material	Metal
Input Current (Starting)	1.5	Housing	C2
Ballast Factor (Nom)	0.93	Housing Dimensions	1.06" x 1.59" x 1.81"
Power Factor (Nom)	0.49	<b>Approval and Application</b>	
Input Current (Nom)	0.27 A	EMC Immunity Standard	FCC Non-Consumer
Input Power (Nom)	16 W		

## Standard

Approval Marks	CSA certificate UL certificate RoHS Compliant
Hum And Noise Level	A
UL Recognized	No
<b>Product Data</b>	
Order product name	STANDARD MAG BALLAST (1) 13W COMPACT(2-PIN) 120V

EAN/UPC - Product	781087048184
Order code	913700507251
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	50
Material Nr. (12NC)	913700507251
Net Weight (Piece)	0.295 kg

## Dimensional drawing



MAG BALLAST (1) 13W COMPACT(2-PIN) 120V

Product	A1	A2	B1	C1	D1
STANDARD MAG BALLAST (1) 13W COMPACT(2-PIN) 120V	3.06 in	2.75 in	1.81 in	1.59 in	0.19 in

