



# Core & Coil (71A) HPS ~LT~ 200W

## CORE & COIL HID HPS BAL 100W S54 480V KIT

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

### Product data

General Information		Electrical	
ANSI Code	S54	Input Frequency	60 Hz
Lamp Type	100W HPS	Input Current (Open Circuit)	0.55 A
Number of Lamps	1 piece/unit	Input Current (Starting)	0.35 A
Circuit Type	HX-HPF	Input Current (Short Circuit)	0.2-0.35 A
Ballast Type	Magnetic HID	Secondary Short Circuit Current	2.6-3.2 A
Base Model	71A8041	Constant Wattage Deviation	Within Trapezoid
Core Size	3 X 4 (2 coil)	Ballast Factor (Nom)	1
Suitable For Outdoor Use	Yes	Power Factor (Nom)	0.90
Ignitor Catalog Number	LI551-H4	Open Circuit Voltage	120 V
Ignitor Temperature Rating	105°C	Input Current (Nom)	0.29 A A
Capacitor Value	10 MFD	Input Power (Nom)	130 W
Capacitor Catalog Number	7C100M30RA	Rated Lamp Power	100 W
Capacitor Requirements	280V	Wiring	
Capacitor Temperature Rating	105°C	Wire Striplength	0.5 mm
Capacitor Diameter/Oval Dimensions	1.65 in	Wire Length by Color	12"
Capacitor Height	2.75 in	Wire Type	Stranded
Automatic Restart	No	Remote Wiring Configuration Allowed	Yes
Operating and Electrical		Max Ballast-Lamp Distance Remote Wiring 2'	
Input Voltage	480 V	Recommended Fuse Value	3 A

## Core & Coil (71A) HPS ~LT~ 200W

### Approval and Application


Open Circuit Voltage Test (Volts)	110-130 V
Approval Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	E
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029E

### Product Data

Order product name	CORE & COIL HID HPS BAL 100W S54 480V KIT
--------------------	--

EAN/UPC - Product	781087027356
Order code	913700538309
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913700538309
Net Weight (Piece)	3.570 kg

### Dimensional drawing



HPS BAL 100W S54 480V KIT

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID HPS BAL 100W S54 480V KIT	3.6 in	2.25 in	3.9 in	3.5 in	2.8 in	2.4 in

