



# Halogen FastFit

## Hi-Brite 7016G 1200W 80V FastFit

Halogen FastFit lamps are replaced in seconds - thanks to the specially designed base. The compact filament ensures high beam intensity, while the shock-resistant design allows easy handling and reliable use in moving head systems. In addition, the highly innovative P3 technology allows use at higher temperatures, which further extends lifetime and consistency of light output. P3 technology also allows the lamp to be used in any burning position and enables more compact designs of fixtures. And because the FastFit design is also applied to Philips MSR/MSD Gold™ lamps, switching lamp technologies is also quick and easy.

### Product data

General Information	
Cap-Base	PGJX50 [PGJX50]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	200 hour(s)

Operating and Electrical	
Power Consumption	1,200 W
Voltage (Nom)	80 V
Voltage (Nom)	80 V

Controls and Dimming	
Dimmable	Yes


  

Mechanical and Housing	
Bulb Finish	Clear

Product Data	
Full product code	871150050707525
Order product name	Hi-Brite 7016G 1200W 80V FastFit
Order code	924575228928
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	924575228928
Full product name	Hi-Brite 7016G 1200W 80V FastFit
EAN/UPC - Case	8711500507082
EAN/UPC - Product/Case	8711500507075

# Halogen FastFit

## Dimensional drawing



Product	D (max)	H	W	L	C (max)	E (max)
Hi-Brite 7016G 1200W 80V	25 mm	10.5 mm	11.7 mm	82 mm	140 mm	41 mm
FastFit						

