



Rough / Vibration Service

100A/RS/Vs/BR/TG 120/130V

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. Rough Service incandescent lamps have an exceptionally strong filament for which a special filament wire is used, which makes these lamps extremely suitable for places where shocks, bumps and vibrations frequently occur. The clear version, with its completely visible filament, is a brilliant light source, whereas the inside-frosted lamp is used wherever well diffused light is required.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent

Light Technical	
Luminous Flux	1,230 lumen


Operating and Electrical	
Power Consumption	100 W
Starting Time (Nom)	0.0 s
Voltage (Nom)	120-130 V

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	A21 [A 21mm]

Product Data	
Order product name	100A/RS/Vs/BR/TG 120/130V
Order code	925286135504
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	60
Material Nr. (12NC)	925286135504
Full product name	100A/RS/Vs/BR/TG 120/130V
EAN/UPC - Case	50046677159271
EAN/UPC - Product/Case	046677159276

Rough / Vibration Service

Dimensional drawing



Product

100A/RS/VS/BR/TG 120/130V

