



InteGrade LED fixtures NB

InteGrade FIX vis 1500mm(59") 840 NB CTR

InteGrade LED fixtures NB enable easy creation of narrow-beam lighting solutions in chillers with doors. The narrow beam in combination with the extremely small dimensions makes this system suitable for integration in doors and mullions where there is no room to place a sizable lighting solution. The unique optical system directs the light precisely where you want it, thus making optimum use of the light and energy. Our LEDs have minimal output degradation and color shift, so the light remains consistent throughout their long lifetime. InteGrade LED is an ideal solution for high-quality lighting without flicker or color differences. The fixture consists of a profile with LED engines and inline locks. Mounting accessories, cables and LED power driver are available separately.

Product data

General Information	
Lighting Technology	LED
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	2,300 lm
Life to 70% Lumen Maintenance	50,000 hour(s)
Color Consistency Initial	<6
Correlated Color Temperature (Nom)	4100 K
Luminous Efficacy (rated) (Nom)	70 lm/W
Color rendering index (CRI)	85
Operating and Electrical	
Power Consumption	34 W


Temperature	
Ambient temperature range	-30 °C to 30 °C
Mechanical and Housing	
Product Length	1,500 mm
Approval and Application	
Approval Marks	CE marking UL certificate
Product Data	
Order product name	InteGrade FIX vis 1500mm(59") 840 NB CTR
Full product name	InteGrade FIX vis 1500mm(59") 840 NB CTR
Full product code	871829167085800
Order code	929000654713
Material Nr. (12NC)	929000654713

InteGrade LED fixtures NB

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291670858
Numerator - Packs per outer box	6

EAN/UPC - Case	8718291670865
----------------	---------------

Dimensional drawing



Product	C (max)	A (max)	B1	B2
InteGrade FIX vis 1500mm(59") 840 NB CTR	25.0 mm	1,500.0 mm	31.0 mm	14.0 mm

