

PHILIPS

Wall light

Linea

SHELLLINE 3000K

white

LED



31238/31/P1



Light and relaxed

Philips myLiving Decolinea Shellline batten wall light combines performance and looks with its simple design. With long-life LED technology and up to 15,000 hours of usage, this light is the ideal replacement for the traditional T5 batten.

Sustainable light solutions

- Energy saving
- High quality LED light
- Long operating life of up to 15 years
- Philips offers a 5-year warranty on the LED module and driver

Highlights

Energy saving



This Philips energy-saving lamp conserves energy compared with traditional light sources, helping you to save money on your electricity bills and do your bit for the environment.

High quality LED light



The LED light bulb delivered with this Philips lamp is a unique solution developed by Philips. It turns on instantly, enables an optimal light output and brings out vivid colours in your home.

Long operating life



A light source you can trust. The integrated LEDs used in this Philips LED lamp will last up to 15,000 hours (which equals 15 years on the basis of an average use of 3 hours/day with at least 13,000 on/off switching cycles). It feels so good to think that you won't have to worry about maintenance or light bulb replacement while having the perfect light ambience in your home.

5-year warranty on LED system



On top of the standard 2-year warranty for this lamp, Philips offers a 5-year warranty on the LED system, meaning the LED module and the driver in this lamp.

Specifications

Design and finishing

- Colour: white
- Material: synthetics

Extra feature/accessory incl.

- Diffused light effect: Yes
- LED integrated: Yes

Miscellaneous

- Especially designed for: Living Room and Bedroom, Kitchen
- Style: Contemporary
- Type: Wall light
- EyeComfort: No

Power consumption

- Energy efficiency label (EEL): A+

Product dimensions and weight

- Height: 3.4 cm
- Length: 60.5 cm
- Net weight: 0.112 kg
- Width: 2.8 cm

Service

- Warranty: 5 year(s)

Technical specifications

- Lifetime up to: 15,000 h
- Total lumen output fixture: 900 lm
- Mains power: Range 220 V–240 V, 50–60 Hz
- Fixture dimmable: No
- LED: Yes
- Number of bulbs: 1
- Wattage bulb included: 9 W
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: II – double insulated



Issue date: 2023-11-08
Version: 0.546

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com