


PHILIPS

Ledinaire Waterproof

WT060C



50Hz
60Hz

220V
240V

LIFE
L65
50K hrs

IP65

IK08

Ta
40 °C
-20 °C

GLOW
WIRE
850 °C



System lumen
(Lm)

CCT








P(W)

A

A-TW1




WT060C LED18S/840 PSU L600	-	1800		16.5	627		0.21
WT060C LED18S/840 PSU TW1 L600	•					689	0.30
WT060C LED36S/840 PSU L1200	-	3600	4000k	33	1186		0.39
WT060C LED36S/840 PSU TW1 L1200	•					1249	0.51
WT060C LED56S/840 PSU L1500	-	5600		51	1466		0.47
WT060C LED56S/840 PSU TW1 L1500	•					1529	0.58




- The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.
- LED board & led driver are not serviceable and not replaceable.
- The light source of this luminaire is not replaceable; when the light source reaches its end of life the whole luminaire shall be replaced



ATTENTION
OBSERVE PRECAUTIONS
FOR HANDLING
ELECTROSTATIC
SENSITIVE
DEVICES



Inrush current



	LED18S	LED36S	LED56S
Electrical characteristics			
I_{nom} (mA)	75	150	235
I_{max} (A)	37	37	37
T_{ref} (μs)	1	1	1
MCB	Luminaire Max.		
B-10 A	10	10	10
B-16 A	10	10	10
C-10 A	10	10	10
C-16 A	10	10	10