

# PHILIPS

Recessed downlight


Hue White Ambiance

Dimmer switch included

GU10

Chrome

Smart control with Hue Bridge\*



34075/11/P7



## Easy smart lighting

With Philips Hue White Ambiance bathroom downlights included in your Philips Hue system and enjoy light recipes that helps you energise, concentrate, read and relax. With the dimmer switch you easily create the right ambience for all your moments.

### Limitless possibilities

- Water-resistant smart light for bathrooms
- Wireless control with included dimmer switch
- Enjoy the right smart lighting for daily tasks

### Full control from a smart device with the Hue bridge

- Full control from a smart device with the Hue bridge

# Highlights

## Water-resistant for bathrooms



The Philips Hue Adore series of smart bathroom lights have been rigorously tested to ensure that they are water resistant, making them ideal for humid environments. Each Adore bathroom light meets IP44 standards.

## Wireless control




With the battery-powered dimmer switch, you can control up to 10 smart lights simultaneously. The switch – which can be removed from its wall mount and used as a remote control – allows you to dim and brighten your lights or cycle through four preset light recipes

## Enjoy the right smart lighting



Maximise the effect of your daily routines with tunable white light. Set the light to match different needs and moods in the bathroom with the press of a button. Get energised in the morning with cool daylight, use the bright light for tasks requiring precision, use the reading light to enjoy a book in the bath or enjoy some me-time in the tub under the warm light.

## Full control with the Hue bridge



Connect your Philips Hue lights with the bridge to unlock the endless possibilities of the system.

# Specifications

## Design and finishing

- Colour: chrome
- Material: synthetics

## Extra feature/accessory incl.

- Dimmable with remote control: Yes
- Hue Switch: Yes
- LED lamp(s) included: Yes

## Miscellaneous

- Especially designed for: Bathroom
- Style: Functional
- Type: Recessed spot light
- EyeComfort: Yes

## Power consumption

- Energy efficiency label (EEL): A

**Product dimensions and weight**

- Cut out length: 7.0 cm
- Cut out width: 7.0 cm
- Length: 9.5 cm
- Net weight: 0.480 kg
- Recessed distance: 8.7 cm
- Width: 9.5 cm

**Service**

- Warranty: 2 year(s)

**Technical specifications**

- Lifetime up to: 15,000 h
- Total lumen output fixture (hidden): 1,050 lm
- Lumen output bulb included: 350 lm
- Light source equivalent to traditional bulb of: 50 W
- Total lumen output fixture: 500 lm
- Bulb technology: LED, 230 V
- Light colour: 2200-6500 Hue White Ambiance
- Number of bulbs 2: 1
- Fitting/cap 2: GU10
- Wattage bulb included 2: 5 W
- Maximum wattage replacement bulb 2: 5.5 W
- Number of bulbs 3: 1
- Wattage bulb included 3: 5 W
- Maximum wattage replacement bulb 3: 5.5 W
- Mains power: 50-60 Hz
- Fixture dimmable: Yes
- LED: Yes
- Built-in LED: No
- Energy class included light source: A
- Fixture is compatible with bulb(s) of class: A+ to E
- Number of bulbs: 3
- Fitting/cap: GU10
- Wattage bulb included: 5 W
- Maximum wattage replacement bulb: 5.5 W
- IP code: IP44
- Class of protection: II - double insulated
- Light source replaceable: Yes



Issue date: 2023-11-08  
Version: 0.576

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)