


# PHILIPS

Recessed spot light

59261 ERIDANI 100 5W 65K WH

white

LED



59261/31/H4



## Essential lighting for a bright home

The Philips Eridani LED Downlight is a flawless fit for a brilliant atmosphere. A soft, elegant cut in white evokes a simple touch for any home setting, accentuating intricate interiors of small corners and compact homes.

### Match your interior style

- Available in various sizes

### Light effect

- Even light distribution

### Sustainable light solutions

- High quality LED light

### Easy to Experience

- Long-lasting, high-powered LED technology

### Energy saving

- Instant, flicker-free start
- Built-in Philips conventional ballast
- Built-in LED, as part of the system
- 80% energy saving

# Highlights

**Available in various sizes**  
**Even light distribution**



**High quality LED light**



The LED technology, integrated into this Philips lamp, is a uniquely developed solution by Philips. While instantly turned on, it enables an optimal light output and brings out vivid colors in your home.

**High-powered LED**



**Instant, flicker-free start**

Instant, flicker-free start, with an electronic ballast

**Energy efficient, long lasting**  
**Integrated LED light source**



A light source you can trust. With integrated LED light source, you won't have to worry about maintenance or lamp replacement while having the perfect light ambiance in your home.

**80% energy saving**



Up to 80% energy saving compared to standard incandescent light sources.

# Specifications

## Design and finishing

- Color: white
- Material: metal/plastic

## Extra feature/accessory incl.

- Adjustable spot head: No
- Diffused light effect: Yes
- Dimmable with remote control: No
- LED integrated: Yes
- Photometric data available: Yes
- Remote control included: No
- Centerpiece: No

## Light characteristics

- Beam angle: 110 degree(s)
- Color rendering index (CRI): 80

## Miscellaneous

- Especially designed for: Functional
- Style: Functional
- Type: Downlight
- EyeComfort: No

## Product dimensions & weight

- Cut out length: 10 cm
- Cut out width: 10 cm
- Height: 5.1 cm
- Length: 11.2 cm
- Net weight: 0.08 kg
- Recessed distance: 5 cm
- Width: 11.2 cm

### Service

- Warranty: 1 year(s)

### Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 112 mm
- Total lumen output fixture: 430
- Light color: 6500
- Mains power: 220–240
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Number of bulbs: 1
- Wattage bulb included: 5
- Maximum wattage replacement bulb: 5 W
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: Class II

### Packaging dimensions and weight

- EAN/UPC – product: 6947830438426
- Net weight: 0.080 kg
- Gross weight: 0.117 kg
- Height: 11.500 cm
- Length: 11.500 cm
- Width: 6.600 cm
- Material number (12NC): 915005573501



Issue date: 2023-11-08  
Version: 0.425

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)