

PHILIPS

Wireless dimming kit
E27

Hue White

1 x E27 Bulb

Warm white light

Dimmable

Dimmer switch included



8718696452523



Dimmable light

Get started with Philips Hue wireless dimming kit and enjoy smooth wireless dimming. It works straight out of the box. Control the lamp with the included dimmer switch, or connect everything to the Hue bridge to unlock more smart features.

Limitless possibilities

- Brighten and dim your smart lights
- Expand to a smart light system with the Hue Bridge
- Mount the dimmer switch anywhere
- Connect up to 10 smart lights

Highlights

Brighten and dim your lights



The Philips Hue Dimmer switch allows you to wirelessly turn your lights up high or down low.

Mount anywhere



The Philips Hue Dimmer switch functions as a normal wall switch and dimmer – but better. In addition to mounting with screws or strong adhesive tape, you can remove the magnetic control and carry it with you anywhere.

Expand with Hue Bridge



When connected to a Hue Bridge (*sold separately), your smart lights become even more versatile. Control your lights from anywhere inside and outside your home using just the Philips Hue app. Set timers, routines and add or remove lights from your system.

Connect up to 10 smart lights



With the Philips Hue wireless dimming kit for smart lights, you can connect up to 10 lights to control simultaneously from a single dimmer switch.

Specifications

Lamp dimensions

- Dimensions (WxHxD): 113*62

Environmental

- Operational humidity: 5% <H<95% (non-condensing)
- Operational temperature: -10°C – 45°C

Guarantee

- 2 years: Yes

Power consumption

- Energy efficiency label (EEL): A+

Service

- Warranty: 2 year(s)

Technical specifications

- Weight: 67
- Bulb technology: LED

The bulb

- Colour temperature: 2700K
- Energy efficiency label: A+
- Fitting: E27 screw base fitting
- Form factor: A60
- Height: 110 mm
- Input voltage: 220V-240V
- Lifetime: 25,000 h
- Light output: Warm white light
- Lumen output: 800 lm
- Max. operation power: 9 W
- Max. standby power: 0.5 W
- Number of switching cycles: 50,000
- Power factor: >0.5
- Rated lifetime: 25,000 h
- Software upgradable: when connected to Hue bridge
- Start up: Instant 100% light output
- Wattage: 9 W
- Wattage equivalent: 60 W
- Width: 61 mm
- Communication protocol: Zigbee
- Software upgradable: When connected to Hue Bridge

The switch

- Batteries included: 1 x CR2450
- Frequency band: 2400 - 2483.5 MHz
- IP rating: 20
- Lifetime: 50000 clicks
- Max. lights per switch: 10 if not linked to Hue bridge
- Minimal battery lifetime: 3 a
- Mounting options: freestanding
- Special features: Not applicable
- Switch depth: 11 mm
- Switch height: 92 mm
- Switch width: 35 mm
- Wall plate depth: 14 mm
- Wall plate height: 115 mm
- Wall plate width: 70 mm
- Weight including wall plate: 67 g
- Weight of switch: 37 g
- Zigbee Light link: IEEE 802.15.4 Protocol

What's in the box

- Hue bulbs: 1
- Hue dimmer switch: 1

What's supported

- HomeKit compatible: Yes
- IOS: 7 or later
- Philips Hue App: Android 7.0 and later
- Voice assistants: Amazon Alexa



Issue date: 2023-11-08
Version: 0.642

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com