



# Coffaire Fluorescent HP

## High Performance Recessed Fluorescent Direct/Indirect – 2' x 2' with Perforated Basket, Static with 2 T5HO 24 watt lamps

High Performance Recessed Fluorescent Direct/Indirect – 2' x 2' with Perforated Basket, Static with 2 T5HO 24 watt lamps

Coffaire HP (High Performance): Our new high-performance Coffaire HP luminaire features a high 95% reflectance white powder painted body, our new Transoptix lens and a 95% reflectance MIRO aluminum reflector. Achieving efficiencies 20% greater than comparable luminaires currently available in the market.

### Product data

General Information	
Lamp Envelope Code	T-5
Lamp Source Code	Fluorescent
Lamp Watts	24
Number of Lamps	2
Operating and Electrical	
Voltages	277 V
Mechanical and Housing	
Fixture Size	2 ft x 2 ft

Product Data	
Order product name	High Performance Recessed Fluorescent Direct/Indirect – 2' x 2' with Perforated Basket, Static with 2 T5HO 24 watt lamps
Order code	CFS2GHP224UNVPG
Material Nr. (12NC)	CFI00001567
Catalog Number	CFS2GHP224UNVPG
Catalog Number Description	High Performance Recessed Fluorescent Direct/Indirect – 2' x 2' with Perforated Basket, Static with 2 T5HO 24 watt lamps