



产品描述

MASTERColour CDM-T 精锐型

单端高光效陶瓷金属卤化物放电灯

优点

- 高流明输出和极高的显色性对商品有杰出的表现力，是促进商品销售的有力工具
- 在寿命周期内保持稳定出色的光色品质，维持店铺的统一形象
- 超高光效、超长寿命可以降低热辐射及店铺维护成本，提高店内环境的舒适度
- UV 防护，降低商品褪色风险

特点

- 清新纯净的白光
- 优异的显色性(Ra90)
- 整个寿命期间表现可靠
- 超级稳定的色彩表现,对红色表现优异(Ra=40)
- 相比普通陶瓷金卤灯光输出及流明维持率大幅提高

应用

- 商业连锁店铺情景及展示照明的最佳方案
- 室外装饰泛光照明
- 必须用在有前置玻璃的封闭式灯具(IEC 61167 and IEC60958)
- 推荐配套电子镇流器使用

安全提示


- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with electronic control gear. 35W & 70W lamps may also use electromagnetic gear.
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTERCoulour CDM-T 精锐型

Versions



二维绘图



Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERC CDM-T Elite 100W/930 G12 1CT/12	20 mm	8.5 mm	55 mm	57 mm	56 mm	110 mm
MASTERC CDM-T Elite 35W/930 G12 1CT/12	20 mm	4.8 mm	55 mm	57 mm	56 mm	103 mm
MASTERC CDM-T Elite 35W/930 G12 1CT/12	20 mm	4.8 mm	55 mm	57 mm	56 mm	103 mm
MASTERC CDM-T Elite 50W/930 G12 1CT/12	20 mm	6 mm	55 mm	57 mm	56 mm	103 mm
MASTERC CDM-T Elite 50W/942 G12 1CT	20 mm	7.1 mm	55 mm	57 mm	56 mm	103 mm
MASTERC CDM-T Elite 70W/930 G12 1CT/12	20 mm	7.15 mm	55 mm	57 mm	56 mm	103 mm
MASTERC CDM-T Elite 70W/930 G12 1CT/12	20 mm	7.15 mm	55 mm	57 mm	56 mm	103 mm

一般信息

底盖	G12
操作位置	UNIVERSAL

控制和调光

可调光	否
-----	---

机械和外壳

灯泡外观	透明
灯泡外形	T19

灯技术

Order Code	Full Product Name	色度坐标 X (标称)	色度坐标 Y (标称)	颜色名称	相关色温 (标称)	显色指数 (CRI)	光效 (额定)(标称)	光通量
928183205125	MASTERC CDM-T Elite 100W/930 G12 1CT/12	0.434	0.398	暖白色 (WW)	3000 K	92	110 lm/W	11,000 lm
928185205129	MASTERC CDM-T Elite 35W/930 G12 1CT/12	0.435	0.395	暖白色 (WW)	3000 K	90	98 lm/W	-
928185205131	MASTERC CDM-T Elite 35W/930 G12 1CT/12	0.434	0.398	暖白色 (WW)	3000 K	90	98 lm/W	4,050 lm
928185305129	MASTERC CDM-T Elite 70W/930 G12 1CT/12	0.435	0.396	暖白色 (WW)	3000 K	90	103 lm/W	-
928185305131	MASTERC CDM-T Elite 70W/930 G12 1CT/12	0.434	0.398	暖白色 (WW)	3000 K	90	103 lm/W	7,800 lm

MASTERC colour CDM-T 精锐型

Order Code	Full Product Name	色度坐标 X (标称)	色度坐标 Y (标称)	颜色名称	相关色温 (标称)	显色指数 (CRI)	光效 (额定)(标称)	光通量
928080015131	MASTERC CDM-T Elite 50W/942 G12 1CT	0.371	0.366	冷白色 (CW)	4200 K	90	100 lm/W	5,000 lm
928191705131	MASTERC CDM-T Elite 50W/930 G12 1CT/12	0.434	0.398	暖白色 (WW)	3000 K	90	108 lm/W	5,450 lm

操作和电气

Order Code	Full Product Name	电压 (标称)	功耗
928183205125	MASTERC CDM-T Elite 100W/930 G12 1CT/12	88 V	100.1 W
928185205129	MASTERC CDM-T Elite 35W/930 G12 1CT/12	85 V	39.1 W
928185205131	MASTERC CDM-T Elite 35W/930 G12 1CT/12	85 V	39.1 W
928185305129	MASTERC CDM-T Elite 70W/930 G12 1CT/12	85 V	73.2 W

Order Code	Full Product Name	电压 (标称)	功耗
928185305131	MASTERC CDM-T Elite 70W/930 G12 1CT/12	85 V	73.2 W
928080015131	MASTERC CDM-T Elite 50W/942 G12 1CT	91 V	50.2 W
928191705131	MASTERC CDM-T Elite 50W/930 G12 1CT/12	90 V	50.2 W

审批和申请

Order Code	Full Product Name	能耗 kWh/1000 h	汞 (Hg) 含量 (最高)	汞 (Hg) 含量 (标称)
928183205125	MASTERC CDM-T Elite 100W/930 G12 1CT/12	101 kWh	10.1 mg	10.1 mg
928185205129	MASTERC CDM-T Elite 35W/930 G12 1CT/12	43 kWh	-	4.7 mg
928185205131	MASTERC CDM-T Elite 35W/930 G12 1CT/12	40 kWh	4.7 mg	4.7 mg
928185305129	MASTERC CDM-T Elite 70W/930 G12 1CT/12	80 kWh	-	6.6 mg
928185305131	MASTERC CDM-T Elite 70W/930 G12 1CT/12	74 kWh	6.6 mg	6.6 mg
928080015131	MASTERC CDM-T Elite 50W/942 G12 1CT	51 kWh	5.7 mg	5.7 mg
928191705131	MASTERC CDM-T Elite 50W/930 G12 1CT/12	51 kWh	6.6 mg	6.6 mg

