



# Smart HID downlight MBS070-074 – a reliable way to create outstanding lighting

## Basic HID MBS070

Our Smart HID downlight is a reliable and flexible solution offering a variety of designs with CDM lamps driven by electromagnetic or electronic gear. With its high lumen output, high energy efficacy, high color rendering index and tight focus, Smart HID downlight is ideally suited to accent lighting in shops or hotels. Its elegant design guarantees a perfect fit in any retail or hospitality environment. And because the housing is adjustable and rotatable, installation couldn't be any simpler.

### Benefits

- No worries about safety and reliability
- Easy to select and to use
- Affordable; low initial cost

### Features

- CCC-certified; truly safe and reliable
- Choice of designs, gear and CDM lamp types
- Adjustable and rotatable for ease of application; easy lamp replacement
- Elegant design; integrates perfectly into shop and hotel environments

### Application

- Shops
- Hotels

### Specifications

## Basic HID MBS070

<b>Type</b>	MBS070 (round, adjustable version)
	MBS071 (round, adjustable and rotatable version)
	MBS072 (round, fixed version)
	MBS073 (square, adjustable version)
	MBS074 (square, fixed version)
<b>Light source</b>	HID:
	- 1 x MASTERColour CDM-R / E27 / 70 W
	- 1 x MASTERColour CDM-T / G12 / 70 W
	- 1 x MASTERColour CDM-TD / RX7s / 70 W
<b>Lamp included</b>	No

<b>Lamp position</b>	Vertical or horizontal
<b>Ballast</b>	Electronic, High Frequency 220-240 V / 50-60 Hz:
	- Electronic
<b>Optic</b>	Wide or medium beam
<b>Optical cover</b>	Safety glass, not for the CDM-R type (MBS070)
<b>Material</b>	Housing: spun aluminum
	Optic: spun aluminum
<b>Color</b>	White
<b>Installation</b>	Fixation by means of spring fasteners
<b>Maintenance</b>	Lamp accessible after removing the glass

## Versions



MBS070 1xCDM-R30-70W

