



Den rimelige løsningen med LEDspot

CorePro LEDspot LV

CorePro LED egner seg perfekt for spotbelysning og gir et varmt halogenlignende lys. Lyskildene er kompatible med de fleste eksisterende armaturer med MR16 GU5.3-holdere, og er utformet som en ettermonterbar erstatning av halogen- eller glødelamper. LED-lyskilder gir store energibesparelser og reduserer vedlikeholdskostnadene

Fordeler

- opptil 80 % energibesparelse sammenlignet med halogenlamper
- Lavere vedlikeholdskostnader
- Bred kompatibilitet med transformatorer

Funksjoner

- Enkelt bytte
- Levetid på 15 000 timer
- UV- og IR-fritt lys
- Uten kvikksølv og farlige materialer

Søknad

- Hoteller, restauranter, barer, kafeer, museer, butikker
- Lobbyer, korridorer, trappehus, vaskerom, resepsjonsområder, utstillinger, utstillingsmontre

CorePro LEDspot LV

Versions



MASTER LEDspot LV 35W GU5-3
827 36D VLE





LEDspots Corepro SLR 2 MR16
GU5,3



LEDspot GU4 Classic MR11

Målskisse



Product	D	C
CorePro LED spot ND 2.9-20W MR16 827 36D	50,5 mm	45,5 mm
CorePro LED spot ND 4.4-35W MR16 827 36D	50,5 mm	45,5 mm
CorePro LED spot ND 4.4-35W MR16 840 36D	50,5 mm	45,5 mm
CorePro LED spot ND 7-50W MR16 827 36D	50,5 mm	45 mm
CorePro LED spot ND 7-50W MR16 840 36D	50,5 mm	45 mm
CorePro LEDspot 4.4-35W MR16 827 36D 5CT	50,5 mm	45,5 mm

Product	D	C
CorePro LED spot 2.3-20W 827 MR11 36D	35,5 mm	39,5 mm

CorePro LEDspot LV

Generell informasjon	
Brytersyklus	50 000
Teknisk belysning	
Spredningsvinkel (nom.)	36 grad(er)
Fargegjengivelsesindeks (CRI)	80
Nominell vedlikeholdsfaktor for lyskildelumen ved utgangen av nominell levetid (nom.)	70 %
Drift og elektronikk	
Inngangsfrekvens	- Hz
Line Frequency	- Hz
Starttid (nom.)	0,5 s
Kontroller og dimming	
Kan dimmes	Nei

Generell informasjon

Order Code	Full Product Name	Sokkelbase	Nominell levetid
30706300	CorePro LED spot ND 4.4-35W MR16 827 36D	GU5.3	15 000 time(r)
30758200	CorePro LEDspot 4.4-35W MR16 827 36D 5CT	GU5.3	15 000 time(r)
30708700	CorePro LED spot ND 4.4-35W MR16 840 36D	GU5.3	15 000 time(r)
81471000	CorePro LED spot ND 7-50W MR16 827 36D	GU5.3	15 000 time(r)
81479600	CorePro LED spot ND 7-50W MR16 840 36D	GU5.3	15 000 time(r)
30704900	CorePro LED spot ND 2.9-20W MR16 827 36D	GU5.3	15 000 time(r)
65948600	CorePro LED spot 2.3-20W 827 MR11 36D	GU4	25 000 time(r)

Teknisk belysning

		Korrelert			
	Full Product	fargetemperatur			Lysintensitet
Order Code	Name	(nom)	Fargekode	Lysytelse	(nom.)
30706300	CorePro LED spot ND 4.4-35W MR16 827 36D	2700 K	827	345 lm	650 cd
30758200	CorePro LEDspot 4.4-35W MR16 827 36D 5CT	2700 K	827	345 lm	650 cd
30708700	CorePro LED spot ND 4.4-35W MR16 840 36D	4000 K	840	390 lm	750 cd
81471000	CorePro LED spot ND	2700 K	827	621 lm	1 400 cd

		Korrelert			
	Full Product	fargetemperatur			Lysintensitet
Order Code	Name	(nom)	Fargekode	Lysytelse	(nom.)
	7-50W MR16 827 36D				
81479600	CorePro LED spot ND 7-50W MR16 840 36D	4000 K	840	660 lm	1 500 cd
30704900	CorePro LED spot ND 2.9-20W MR16 827 36D	2700 K	827	230 lm	560 cd
65948600	CorePro LED spot 2.3-20W 827 MR11 36D	2700 K	827	184 lm	400 cd

Drift og elektronikk

Order Code	Full Product Name	Effekten som	
		Effektforbruk	tilsvarer
30706300	CorePro LED spot ND 4.4-35W MR16 827 36D	4,4 W	35 W
30758200	CorePro LEDspot 4.4-35W MR16 827 36D 5CT	4,4 W	35 W
30708700	CorePro LED spot ND 4.4-35W MR16 840 36D	4,4 W	35 W
81471000	CorePro LED spot ND 7-50W MR16 827 36D	7 W	50 W

Order Code	Full Product Name	Effekten som	
		Effektforbruk	tilsvarer
81479600	CorePro LED spot ND 7-50W MR16 840 36D	7 W	50 W
30704900	CorePro LED spot ND 2.9-20W MR16 827 36D	2,9 W	20 W
65948600	CorePro LED spot 2.3-20W 827 MR11 36D	2,3 W	20 W

Temperatur

CorePro LEDspot LV


Order Code	Full Product Name	Maksimal temperatur for innfatningen (nom.)
30706300	CorePro LED spot ND 4.4-35W MR16 827 36D	85 °C
30758200	CorePro LEDspot 4.4-35W MR16 827 36D 5CT	85 °C
30708700	CorePro LED spot ND 4.4-35W MR16 840 36D	85 °C
81471000	CorePro LED spot ND 7-50W MR16 827 36D	85 °C

Mekanikk og innfatning

Order Code	Full Product Name	Lyspæreoverflate	Lyspæreform
30706300	CorePro LED spot ND 4.4-35W MR16 827 36D	-	MR16
30758200	CorePro LEDspot 4.4-35W MR16 827 36D 5CT	-	MR16
30708700	CorePro LED spot ND 4.4-35W MR16 840 36D	-	MR16
81471000	CorePro LED spot ND 7-50W MR16 827 36D	-	MR16


Godkjenning og bruksområde

Order Code	Full Product Name	Energiforbruk kWh/1000 t
30706300	CorePro LED spot ND 4.4-35W MR16 827 36D	5 kWh
30758200	CorePro LEDspot 4.4-35W MR16 827 36D 5CT	5 kWh
30708700	CorePro LED spot ND 4.4-35W MR16 840 36D	5 kWh
81471000	CorePro LED spot ND 7-50W MR16 827 36D	7 kWh
81479600	CorePro LED spot ND 7-50W MR16 840 36D	7 kWh
30704900	CorePro LED spot ND 2.9-20W MR16 827 36D	3 kWh
65948600	CorePro LED spot 2.3-20W 827 MR11 36D	3 kWh




Order Code	Full Product Name	Maksimal temperatur for innfatningen (nom.)
81479600	CorePro LED spot ND 7-50W MR16 840 36D	85 °C
30704900	CorePro LED spot ND 2.9-20W MR16 827 36D	75 °C
65948600	CorePro LED spot 2.3-20W 827 MR11 36D	60 °C


Order Code	Full Product Name	Lyspæreoverflate	Lyspæreform
81479600	CorePro LED spot ND 7-50W MR16 840 36D	-	MR16
30704900	CorePro LED spot ND 2.9-20W MR16 827 36D	-	MR16
65948600	CorePro LED spot 2.3-20W 827 MR11 36D	Matt	MR11




CorePro LEDspot LV




Accent Diagrams




Accent Diagram - CorePro LED spot ND 2.9-20W MR16 827 36D




Accent Diagram - CorePro LED spot ND 7-50W MR16 840 36D




Accent Diagram - CorePro LED spot ND 7-50W MR16 827 36D



Accent Diagram - CorePro LED spot 2.3-20W 827 MR11 36D




Accent Diagram - CorePro LED spot ND 4.4-35W MR16 840 36D




Accent Diagram - CorePro LEDspot 4.4-35W MR16 827 36D 5CT


Beam Diagrams




Beam diagram - CorePro LED spot 2.3-20W 827 MR11 36D




Beam diagram - CorePro LED spot ND 7-50W MR16 827 36D




Beam diagram - CorePro LED spot ND 7-50W MR16 840 36D



Beam diagram - CorePro LED spot ND 4.4-35W MR16 840 36D



Beam diagram - CorePro LEDspot 4.4-35W MR16 827 36D 5CT



Beam diagram - CorePro LED spot ND 2.9-20W MR16 827 36D

