



For your everyday lighting jobs, CorePro LEDspot mv is the perfect fit for spot lighting GU10 and deliver warm halogen-like light

CorePro LEDspot MV

CorePro LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. These GU10 LED spot lights are compatible with most existing fixtures with a GU10 LED base and are designed as a retrofit replacement for halogen or incandescent spots. CorePro LEDspots deliver significant energy savings and minimize maintenance costs.

Benefits

- Warm white light
- Up to 80% energy saving compared with halogen lamps
- Lower maintenance costs

CorePro LEDspot MV

Features

- Easy retrofit
- Lifetime of 15,000 hours
- Compatible with an extensive range of dimmers
- UV- and IR-free light
- Contain no mercury and hazardous materials – RoHS compliant

Application

- Hospitality
- Retail
- Residential

Versions



LEDspot 50W GU10 830 35D



LEDspot 50W GU10 PAR16
827-865 36D ND




LEDspot ESS 4W E14 R50 827-865
12D ND RCA




LEDspots MV PAR16 GU10

CorePro LEDspot MV

Dimensional drawing







Product	D	C
CorePro LEDspot 3-35W GU10 827 36D DIM	50 mm	54 mm
CorePro LEDspot 3-35W GU10 830 36D DIM	50 mm	54 mm
CorePro LEDspot 3-35W GU10 840 36D DIM	50 mm	54 mm
CorePro LEDspot 4-50W GU10 827 36D DIM	50 mm	54 mm
CorePro LEDspot 4-50W GU10 830 36D DIM	50 mm	54 mm
CorePro LEDspot 4-50W GU10 840 36D DIM	50 mm	54 mm
CorePro LEDspot 4.6-50W GU10 827 36D 5CT	50 mm	54 mm
CoreProLEDspot 3-35W GU10 830 36D DIM UK	50 mm	54 mm
CoreProLEDspot 4-50W GU10 827 36D DIM UK	50 mm	54 mm
CoreProLEDspot 4-50W GU10 830 36D DIM UK	50 mm	54 mm
CoreProLEDspot 4-50W GU10 840 36D DIM UK	50 mm	54 mm
CoreProLEDspot 4-50W GU10 865 36D DIM UK	50 mm	54 mm
Corepro LEDspot 2.7-25W GU10 827 36D	50 mm	53 mm
Corepro LEDspot 2.7-25W GU10 830 36D	50 mm	54 mm
Corepro LEDspot 2.7-25W GU10 840 36D	50 mm	54 mm
Corepro LEDspot 3.5-35W GU10 827 36D	50 mm	54 mm
Corepro LEDspot 3.5-35W GU10 827 36D UK	50 mm	54 mm
Corepro LEDspot 3.5-35W GU10 830 36D	50 mm	54 mm
Corepro LEDspot 3.5-35W GU10 830 36D UK	50 mm	54 mm
Corepro LEDspot 3.5-35W GU10 840 36D	50 mm	54 mm
Corepro LEDspot 3.5-35W GU10 840 36D UK	50 mm	54 mm
Corepro LEDspot 4.6-50W GU10 827 36D	50 mm	54 mm
Corepro LEDspot 4.6-50W GU10 827 36D UK	50 mm	54 mm
Corepro LEDspot 4.6-50W GU10 830 36D	50 mm	54 mm
Corepro LEDspot 4.6-50W GU10 830 36D UK	50 mm	54 mm
Corepro LEDspot 4.6-50W GU10 840 36D	50 mm	54 mm
Corepro LEDspot 4.6-50W GU10 840 36D UK	50 mm	54 mm
Corepro LEDspot 4.6-50W GU10 865 36D	50 mm	54 mm
Corepro LEDspot 4.6-50W GU10 865 36D UK	50 mm	54 mm
Essential LED 4.6-50W GU10 865 36D	50 mm	54 mm



Product	D	C
ESS LEDspot 6W 640lm E14 R50 827	50 mm	86 mm
ESS LEDspot 6W 640lm E14 R50 840	50 mm	86 mm
ESS LEDspot 6W 640lm E14 R50 865	50 mm	86 mm

CorePro LEDspot MV

Dimensional drawing



Product	D	C
ESS LEDspot 9W 980lm E27 R63 827	63 mm	102 mm
ESS LEDspot 9W 980lm E27 R63 840	63 mm	102 mm
ESS LEDspot 9W 980lm E27 R63 865	63 mm	102 mm



Product	D	C
ESS LEDspot 10W 1150lm E27 R80 827	80 mm	115 mm
ESS LEDspot 10W 1150lm E27 R80 840	80 mm	115 mm
ESS LEDspot 10W 1150lm E27 R80 865	80 mm	115 mm

Product	D	C
LEDspot GU10 50W 830 36D 6CT	50 mm	54 mm

Product	D	C
CorePro LEDspot 4.9-65W GU10 830 36D ND	50 mm	54 mm
CorePro LEDspot 4.9-65W GU10 840 36D ND	50 mm	54 mm
Corepro LEDspot 550lm GU10 830 120D	50 mm	54 mm
Corepro LEDspot 550lm GU10 840 120D	50 mm	54 mm
Corepro LEDspot 550lm GU10 865 120D	50 mm	54 mm

CorePro LEDspot MV

Dimensional drawing



Product	D	C
ESSLEDspot 6W 500lm GU10 827 120D ND RCA	50 mm	58 mm
ESSLEDspot 8W 720lm GU10 830 120D ND RCA	50 mm	58 mm
ESSLEDspot 8W 720lm GU10 840 120D ND RCA	50 mm	58 mm

Product	D	C
Corepro LEDspot 670lm GU10 830 60D	50 mm	54 mm
Corepro LEDspot 730lm GU10 840 60D	50 mm	54 mm

Light Technical

Color rendering index (CRI) 80

LLMF At End Of Nominal Lifetime 70 %

(Nom)

Operating and Electrical

Input Frequency 50 to 60 Hz

Line Frequency 50 to 60 Hz

General Information

Order Code	Full Product Name	Cap-Base	Rated		
			Lifetime (Hours)	Switching Cycle	Nominal lifetime
929002065602	CorePro LEDspot 3-35W GU10 840 36D DIM	GU10	-	50,000	15,000 hour(s)
929002068202	CorePro LEDspot 3-35W GU10 830 36D DIM	GU10	-	50,000	15,000 hour(s)
929002068299	CoreProLEDspot 3-35W GU10 830 36D DIM UK	GU10	-	50,000	15,000 hour(s)
929002495802	CorePro LEDspot 3-35W GU10 827 36D DIM	GU10	-	50,000	15,000 hour(s)
929002495902	CorePro LEDspot 4-50W GU10 827 36D DIM	GU10	-	50,000	15,000 hour(s)
929002495999	CoreProLEDspot 4-50W GU10 827 36D DIM UK	GU10	-	50,000	15,000 hour(s)

Order Code	Full Product Name	Cap-Base	Rated		
			Lifetime (Hours)	Switching Cycle	Nominal lifetime
929003562499	CoreProLEDspot 4-50W GU10 865 36D DIM UK	GU10	-	50,000	15,000 hour(s)
929001215232	Corepro LEDspot 4.6-50W GU10 827 36D	GU10	-	50,000	15,000 hour(s)
929001215252	CorePro LEDspot 4.6-50W GU10 827 36D	GU10	-	50,000	15,000 hour(s)
929001215268	Corepro LEDspot 4.6-50W GU10 827 36D UK	GU10	-	50,000	15,000 hour(s)
929001217532	Corepro LEDspot 2.7-25W GU10 827 36D	GU10	-	50,000	15,000 hour(s)

CorePro LEDspot MV

Order Code	Full Product Name	Cap-Base	Rated			Nominal lifetime
			Lifetime (Hours)	Switching Cycle		
929001217862	Corepro LEDspot 3.5-35W GU10 827 36D	GU10	-	50,000	15,000	hour(s)
929001217897	Corepro LEDspot 3.5-35W GU10 827 36D UK	GU10	-	50,000	15,000	hour(s)
929002981202	Corepro LEDspot 550lm GU10 830 120D	GU10	-	50,000	15,000	hour(s)
929002981302	Corepro LEDspot 550lm GU10 840 120D	GU10	-	50,000	15,000	hour(s)
929002981402	Corepro LEDspot 550lm GU10 865 120D	GU10	-	50,000	15,000	hour(s)
929002065802	CorePro LEDspot 4-50W GU10 840 36D DIM	GU10	-	50,000	15,000	hour(s)
929002065899	CoreProLEDspot 4-50W GU10 840 36D DIM UK	GU10	-	50,000	15,000	hour(s)
929002068302	CorePro LEDspot 4-50W GU10 830 36D DIM	GU10	-	50,000	15,000	hour(s)
929002068399	CoreProLEDspot 4-50W GU10 830 36D DIM UK	GU10	-	50,000	15,000	hour(s)
929002981002	CorePro LEDspot 4.9-65W GU10 830 36D ND	GU10	-	50,000	15,000	hour(s)
929002981102	CorePro LEDspot 4.9-65W GU10 840 36D ND	GU10	-	50,000	15,000	hour(s)
929001217602	Corepro LEDspot 2.7-25W GU10 830 36D	GU10	-	50,000	15,000	hour(s)
929001217702	Corepro LEDspot 2.7-25W GU10 840 36D	GU10	-	50,000	15,000	hour(s)
929001217902	Corepro LEDspot 3.5-35W GU10 830 36D	GU10	-	50,000	15,000	hour(s)
929001217999	Corepro LEDspot 3.5-35W GU10 830 36D UK	GU10	-	50,000	15,000	hour(s)
929001218002	Corepro LEDspot 3.5-35W GU10 840 36D	GU10	-	50,000	15,000	hour(s)
929001218099	Corepro LEDspot 3.5-35W GU10 840 36D UK	GU10	-	50,000	15,000	hour(s)
929001218102	Corepro LEDspot 4.6-50W GU10 830 36D	GU10	-	50,000	15,000	hour(s)
929001218199	Corepro LEDspot 4.6-50W GU10 830 36D UK	GU10	-	50,000	15,000	hour(s)

Order Code	Full Product Name	Cap-Base	Rated			Nominal lifetime
			Lifetime (Hours)	Switching Cycle		
929001218202	Corepro LEDspot 4.6-50W GU10 840 36D	GU10	-	50,000	15,000	hour(s)
929001218299	Corepro LEDspot 4.6-50W GU10 840 36D UK	GU10	-	50,000	15,000	hour(s)
929001218302	Corepro LEDspot 4.6-50W GU10 865 36D	GU10	-	50,000	15,000	hour(s)
929001218308	Essential LED 4.6-50W GU10 865 36D	GU10	-	50,000	15,000	hour(s)
929001218399	Corepro LEDspot 4.6-50W GU10 865 36D UK	GU10	-	50,000	15,000	hour(s)
929003132390	LEDspot GU10 50W 830 36D 6CT	GU10	-	15,000	15,000	hour(s)
929002965587	ESS LEDspot 6W 640lm E14 R50 827	E14	15,000	50,000	15,000	hour(s)
929002965687	ESS LEDspot 6W 640lm E14 R50 840	E14	15,000	50,000	15,000	hour(s)
929002965787	ESS LEDspot 6W 640lm E14 R50 865	E14	15,000	50,000	15,000	hour(s)
929002965887	ESS LEDspot 9W 980lm E27 R63 827	E27	15,000	50,000	15,000	hour(s)
929002965987	ESS LEDspot 9W 980lm E27 R63 840	E27	15,000	50,000	15,000	hour(s)
929002966087	ESS LEDspot 9W 980lm E27 R63 865	E27	15,000	50,000	15,000	hour(s)
929002966187	ESS LEDspot 10W 1150lm E27 R80 827	E27	15,000	50,000	15,000	hour(s)
929002966287	ESS LEDspot 10W 1150lm E27 R80 840	E27	15,000	50,000	15,000	hour(s)
929002966387	ESS LEDspot 10W 1150lm E27 R80 865	E27	15,000	50,000	15,000	hour(s)
929002466702	Corepro LEDspot 670lm GU10 830 60D	GU10	-	50,000	25,000	hour(s)
929002466802	Corepro LEDspot 730lm GU10 840 60D	GU10	-	50,000	25,000	hour(s)
929001372017	ESSLEDspot 6W 500lm GU10 827 120D ND RCA	GU10	15,000	30,000	15,000	hour(s)
929002093317	ESSLEDspot 8W 720lm GU10 830 120D ND RCA	GU10	15,000	30,000	15,000	hour(s)
929002093417	ESSLEDspot 8W 720lm GU10 840 120D ND RCA	GU10	15,000	30,000	15,000	hour(s)

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color Code	Luminous Flux	Luminous Intensity (Nom)
929002065602	CorePro LEDspot 3-35W GU10 840 36D DIM	36 degree(s)	4000 K	840	240 lm	500 cd
929002068202	CorePro LEDspot 3-35W GU10 830 36D DIM	36 degree(s)	3000 K	830	230 lm	500 cd

CorePro LEDspot MV

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color Code	Luminous Flux	Luminous Intensity (Nom)
929002068299	CoreProLEDspot 3-35W GU10 830 36D DIM UK	36 degree(s)	3000 K	830	230 lm	500 cd
929002495802	CorePro LEDspot 3-35W GU10 827 36D DIM	36 degree(s)	2700 K	827	230 lm	500 cd
929002495902	CorePro LEDspot 4-50W GU10 827 36D DIM	36 degree(s)	2700 K	827	345 lm	700 cd
929002495999	CoreProLEDspot 4-50W GU10 827 36D DIM UK	36 degree(s)	2700 K	827	345 lm	700 cd
929003562499	CoreProLEDspot 4-50W GU10 865 36D DIM UK	36 degree(s)	6500 K	865	345 lm	700 cd
929001215232	Corepro LEDspot 4.6-50W GU10 827 36D	36 degree(s)	2700 K	827	355 lm	700 cd
929001215252	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	36 degree(s)	2700 K	827	355 lm	700 cd
929001215268	Corepro LEDspot 4.6-50W GU10 827 36D UK	36 degree(s)	2700 K	827	355 lm	700 cd
929001217532	Corepro LEDspot 2.7-25W GU10 827 36D	36 degree(s)	2700 K	827	215 lm	470 cd
929001217862	Corepro LEDspot 3.5-35W GU10 827 36D	36 degree(s)	2700 K	827	255 lm	545 cd
929001217897	Corepro LEDspot 3.5-35W GU10 827 36D UK	36 degree(s)	2700 K	827	255 lm	545 cd
929002981202	Corepro LEDspot 550lm GU10 830 120D	120 degree(s)	3000 K	830	550 lm	-
929002981302	Corepro LEDspot 550lm GU10 840 120D	120 degree(s)	4000 K	840	550 lm	-
929002981402	Corepro LEDspot 550lm GU10 865 120D	120 degree(s)	6500 K	865	550 lm	-
929002065802	CorePro LEDspot 4-50W GU10 840 36D DIM	36 degree(s)	4000 K	840	350 lm	700 cd
929002065899	CoreProLEDspot 4-50W GU10 840 36D DIM UK	36 degree(s)	4000 K	840	350 lm	700 cd
929002068302	CorePro LEDspot 4-50W GU10 830 36D DIM	36 degree(s)	3000 K	830	345 lm	700 cd
929002068399	CoreProLEDspot 4-50W GU10 830 36D DIM UK	36 degree(s)	3000 K	830	345 lm	700 cd
929002981002	CorePro LEDspot 4.9-65W GU10 830 36D ND	36 degree(s)	3000 K	830	460 lm	800 cd
929002981102	CorePro LEDspot 4.9-65W GU10 840 36D ND	36 degree(s)	4000 K	840	485 lm	800 cd
929001217602	Corepro LEDspot 2.7-25W GU10 830 36D	36 degree(s)	3000 K	830	225 lm	490 cd
929001217702	Corepro LEDspot 2.7-25W GU10 840 36D	36 degree(s)	4000 K	840	230 lm	500 cd
929001217902	Corepro LEDspot 3.5-35W GU10 830 36D	36 degree(s)	3000 K	830	265 lm	565 cd
929001217999	Corepro LEDspot 3.5-35W GU10 830 36D UK	36 degree(s)	3000 K	830	265 lm	565 cd
929001218002	Corepro LEDspot 3.5-35W GU10 840 36D	36 degree(s)	4000 K	840	275 lm	590 cd
929001218099	Corepro LEDspot 3.5-35W GU10 840 36D UK	36 degree(s)	4000 K	840	275 lm	590 cd
929001218102	Corepro LEDspot 4.6-50W GU10 830 36D	36 degree(s)	3000 K	830	370 lm	740 cd
929001218199	Corepro LEDspot 4.6-50W GU10 830 36D UK	36 degree(s)	3000 K	830	370 lm	740 cd
929001218202	Corepro LEDspot 4.6-50W GU10 840 36D	36 degree(s)	4000 K	840	390 lm	770 cd
929001218299	Corepro LEDspot 4.6-50W GU10 840 36D UK	36 degree(s)	4000 K	840	390 lm	770 cd
929001218302	Corepro LEDspot 4.6-50W GU10 865 36D	36 degree(s)	6500 K	865	390 lm	770 cd
929001218308	Essential LED 4.6-50W GU10 865 36D	36 degree(s)	6500 K	865	430 lm	770 cd
929001218399	Corepro LEDspot 4.6-50W GU10 865 36D UK	36 degree(s)	6500 K	865	390 lm	770 cd
929003132390	LEDspot GU10 50W 830 36D 6CT	36 degree(s)	3000 K	830	345 lm	700 cd
929002965587	ESS LEDspot 6W 640lm E14 R50 827	120 degree(s)	2700 K	827	640 lm	-
929002965687	ESS LEDspot 6W 640lm E14 R50 840	120 degree(s)	4000 K	840	640 lm	-
929002965787	ESS LEDspot 6W 640lm E14 R50 865	120 degree(s)	6500 K	865	640 lm	-
929002965887	ESS LEDspot 9W 980lm E27 R63 827	120 degree(s)	2700 K	827	980 lm	-
929002965987	ESS LEDspot 9W 980lm E27 R63 840	120 degree(s)	4000 K	840	980 lm	-
929002966087	ESS LEDspot 9W 980lm E27 R63 865	120 degree(s)	6500 K	865	980 lm	-
929002966187	ESS LEDspot 10W 1150lm E27 R80 827	120 degree(s)	2700 K	827	1,150 lm	-
929002966287	ESS LEDspot 10W 1150lm E27 R80 840	120 degree(s)	4000 K	840	1,150 lm	-
929002966387	ESS LEDspot 10W 1150lm E27 R80 865	120 degree(s)	6500 K	865	1,150 lm	-
929002466702	Corepro LEDspot 670lm GU10 830 60D	60 degree(s)	3000 K	830	670 lm	750 cd
929002466802	Corepro LEDspot 730lm GU10 840 60D	60 degree(s)	4000 K	840	730 lm	750 cd
929001372017	ESSLEDspot 6W 500lm GU10 827 120D ND RCA	120 degree(s)	2700 K	827	500 lm	-
929002093317	ESSLEDspot 8W 720lm GU10 830 120D ND RCA	120 degree(s)	3000 K	830	720 lm	-
929002093417	ESSLEDspot 8W 720lm GU10 840 120D ND RCA	120 degree(s)	4000 K	840	720 lm	-

Operating and Electrical

CorePro LEDspot MV

Order Code	Full Product Name	Power Consumption	Starting Time (Nom)	Wattage Equivalent
929002065602	CorePro LEDspot 3-35W GU10 840 36D DIM	3 W	0.5 s	35 W
929002068202	CorePro LEDspot 3-35W GU10 830 36D DIM	3 W	0.5 s	35 W
929002068299	CoreProLEDspot 3-35W GU10 830 36D DIM UK	3 W	0.5 s	35 W
929002495802	CorePro LEDspot 3-35W GU10 827 36D DIM	3 W	0.5 s	35 W
929002495902	CorePro LEDspot 4-50W GU10 827 36D DIM	4 W	0.5 s	50 W
929002495999	CoreProLEDspot 4-50W GU10 827 36D DIM UK	4 W	0.5 s	50 W
929003562499	CoreProLEDspot 4-50W GU10 865 36D DIM UK	4 W	0.5 s	50 W
929001215232	Corepro LEDspot 4.6-50W GU10 827 36D	4.6 W	0.5 s	50 W
929001215252	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	4.6 W	0.5 s	50 W
929001215268	Corepro LEDspot 4.6-50W GU10 827 36D UK	4.6 W	0.5 s	50 W
929001217532	Corepro LEDspot 2.7-25W GU10 827 36D	2.7 W	0.5 s	25 W
929001217862	Corepro LEDspot 3.5-35W GU10 827 36D	3.5 W	0.5 s	35 W
929001217897	Corepro LEDspot 3.5-35W GU10 827 36D UK	3.5 W	0.5 s	35 W
929002981202	Corepro LEDspot 550lm GU10 830 120D	4.9 W	0.5 s	-
929002981302	Corepro LEDspot 550lm GU10 840 120D	4.9 W	0.5 s	-
929002981402	Corepro LEDspot 550lm GU10 865 120D	4.9 W	0.5 s	-
929002065802	CorePro LEDspot 4-50W GU10 840 36D DIM	4 W	0.5 s	50 W
929002065899	CoreProLEDspot 4-50W GU10 840 36D DIM UK	4 W	0.5 s	50 W
929002068302	CorePro LEDspot 4-50W GU10 830 36D DIM	4 W	0.5 s	50 W
929002068399	CoreProLEDspot 4-50W GU10 830 36D DIM UK	4 W	0.5 s	50 W
929002981002	CorePro LEDspot 4.9-65W GU10 830 36D ND	4.9 W	0.5 s	65 W
929002981102	CorePro LEDspot 4.9-65W GU10 840 36D ND	4.9 W	0.5 s	65 W

Order Code	Full Product Name	Power Consumption	Starting Time (Nom)	Wattage Equivalent
929001217602	Corepro LEDspot 2.7-25W GU10 830 36D	2.7 W	0.5 s	25 W
929001217702	Corepro LEDspot 2.7-25W GU10 840 36D	2.7 W	0.5 s	25 W
929001217902	Corepro LEDspot 3.5-35W GU10 830 36D	3.5 W	0.5 s	35 W
929001217999	Corepro LEDspot 3.5-35W GU10 830 36D UK	3.5 W	0.5 s	35 W
929001218002	Corepro LEDspot 3.5-35W GU10 840 36D	3.5 W	0.5 s	35 W
929001218099	Corepro LEDspot 3.5-35W GU10 840 36D UK	3.5 W	0.5 s	35 W
929001218102	Corepro LEDspot 4.6-50W GU10 830 36D	4.6 W	0.5 s	50 W
929001218199	Corepro LEDspot 4.6-50W GU10 830 36D UK	4.6 W	0.5 s	50 W
929001218202	Corepro LEDspot 4.6-50W GU10 840 36D	4.6 W	0.5 s	50 W
929001218299	Corepro LEDspot 4.6-50W GU10 840 36D UK	4.6 W	0.5 s	50 W
929001218302	Corepro LEDspot 4.6-50W GU10 865 36D	4.6 W	0.5 s	50 W
929001218308	Essential LED 4.6-50W GU10 865 36D	4.6 W	0.5 s	50 W
929001218399	Corepro LEDspot 4.6-50W GU10 865 36D UK	4.6 W	0.5 s	50 W
929003132390	LEDspot GU10 50W 830 36D 6CT	4.7 W	0.5 s	50 W
929002965587	ESS LEDspot 6W 640lm E14 R50 827	6 W	0.5 s	50 W
929002965687	ESS LEDspot 6W 640lm E14 R50 840	6 W	0.5 s	50 W
929002965787	ESS LEDspot 6W 640lm E14 R50 865	6 W	0.5 s	50 W
929002965887	ESS LEDspot 9W 980lm E27 R63 827	9 W	0.5 s	70 W
929002965987	ESS LEDspot 9W 980lm E27 R63 840	9 W	0.5 s	70 W
929002966087	ESS LEDspot 9W 980lm E27 R63 865	9 W	0.5 s	70 W
929002966187	ESS LEDspot 10W 1150lm E27 R80 827	10 W	0.5 s	80 W
929002966287	ESS LEDspot 10W 1150lm E27 R80 840	10 W	0.5 s	80 W

CorePro LEDspot MV

Order Code	Full Product Name	Power Consumption	Starting	
			Time (Nom)	Wattage Equivalent
929002966387	ESS LEDspot 10W 1150lm E27 R80 865	10 W	0.5 s	80 W
929002466702	Corepro LEDspot 670lm GU10 830 60D	6.7 W	0.5 s	90 W
929002466802	Corepro LEDspot 730lm GU10 840 60D	6.7 W	0.5 s	100 W

Order Code	Full Product Name	Power Consumption	Starting	
			Time (Nom)	Wattage Equivalent
929001372017	ESSLEDspot 6W 500lm GU10 827 120D ND RCA	5.5 W	0.5 s	-
929002093317	ESSLEDspot 8W 720lm GU10 830 120D ND RCA	7.5 W	0.4 s	-
929002093417	ESSLEDspot 8W 720lm GU10 840 120D ND RCA	7.5 W	0.4 s	-

Temperature

Order Code	Full Product Name	Ambient temperature range	T-Case	
			Maximum (Nom)	Maximum (Nom)
929002065602	CorePro LEDspot 3-35W GU10 840 36D DIM	-	65 °C	
929002068202	CorePro LEDspot 3-35W GU10 830 36D DIM	-	65 °C	
929002068299	CoreProLEDspot 3-35W GU10 830 36D DIM UK	-	65 °C	
929002495802	CorePro LEDspot 3-35W GU10 827 36D DIM	-	65 °C	
929002495902	CorePro LEDspot 4-50W GU10 827 36D DIM	-	70 °C	
929002495999	CoreProLEDspot 4-50W GU10 827 36D DIM UK	-	70 °C	
929003562499	CoreProLEDspot 4-50W GU10 865 36D DIM UK	-20 °C to 45 °C	70 °C	
929001215232	Corepro LEDspot 4.6-50W GU10 827 36D	-	72 °C	
929001215252	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	-	72 °C	
929001215268	Corepro LEDspot 4.6-50W GU10 827 36D UK	-	80 °C	
929001217532	Corepro LEDspot 2.7-25W GU10 827 36D	-	50 °C	
929001217862	Corepro LEDspot 3.5-35W GU10 827 36D	-	65 °C	
929001217897	Corepro LEDspot 3.5-35W GU10 827 36D UK	-	75 °C	
929002981202	Corepro LEDspot 550lm GU10 830 120D	-	85 °C	
929002981302	Corepro LEDspot 550lm GU10 840 120D	-	85 °C	
929002981402	Corepro LEDspot 550lm GU10 865 120D	-	85 °C	
929002065802	CorePro LEDspot 4-50W GU10 840 36D DIM	-	70 °C	
929002065899	CoreProLEDspot 4-50W GU10 840 36D DIM UK	-	70 °C	
929002068302	CorePro LEDspot 4-50W GU10 830 36D DIM	-	70 °C	

Order Code	Full Product Name	Ambient temperature range	T-Case	
			Maximum (Nom)	Maximum (Nom)
929002068399	CoreProLEDspot 4-50W GU10 830 36D DIM UK	-	70 °C	
929002981002	CorePro LEDspot 4.9-65W GU10 830 36D ND	-	85 °C	
929002981102	CorePro LEDspot 4.9-65W GU10 840 36D ND	-	85 °C	
929001217602	Corepro LEDspot 2.7-25W GU10 830 36D	-	50 °C	
929001217702	Corepro LEDspot 2.7-25W GU10 840 36D	-	50 °C	
929001217902	Corepro LEDspot 3.5-35W GU10 830 36D	-	65 °C	
929001217999	Corepro LEDspot 3.5-35W GU10 830 36D UK	-	75 °C	
929001218002	Corepro LEDspot 3.5-35W GU10 840 36D	-	65 °C	
929001218099	Corepro LEDspot 3.5-35W GU10 840 36D UK	-	75 °C	
929001218102	Corepro LEDspot 4.6-50W GU10 830 36D	-	72 °C	
929001218199	Corepro LEDspot 4.6-50W GU10 830 36D UK	-	80 °C	
929001218202	Corepro LEDspot 4.6-50W GU10 840 36D	-	72 °C	
929001218299	Corepro LEDspot 4.6-50W GU10 840 36D UK	-	80 °C	
929001218302	Corepro LEDspot 4.6-50W GU10 865 36D	-	72 °C	
929001218308	Essential LED 4.6-50W GU10 865 36D	-20 °C to 45 °C	80 °C	
929001218399	Corepro LEDspot 4.6-50W GU10 865 36D UK	-	80 °C	
929003132390	LEDspot GU10 50W 830 36D 6CT	-	75 °C	
929002965587	ESS LEDspot 6W 640lm E14 R50 827	-	70 °C	
929002965687	ESS LEDspot 6W 640lm E14 R50 840	-	70 °C	

CorePro LEDspot MV

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
929002965787	ESS LEDspot 6W 640lm E14 R50 865	-	70 °C
929002965887	ESS LEDspot 9W 980lm E27 R63 827	-	80 °C
929002965987	ESS LEDspot 9W 980lm E27 R63 840	-	80 °C
929002966087	ESS LEDspot 9W 980lm E27 R63 865	-	80 °C
929002966187	ESS LEDspot 10W 1150lm E27 R80 827	-	85 °C
929002966287	ESS LEDspot 10W 1150lm E27 R80 840	-	85 °C

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
929002966387	ESS LEDspot 10W 1150lm E27 R80 865	-	85 °C
929002466702	Corepro LEDspot 670lm GU10 830 60D	-	75 °C
929002466802	Corepro LEDspot 730lm GU10 840 60D	-	75 °C
929001372017	ESSLEDspot 6W 500lm GU10 827 120D ND RCA	-	68 °C
929002093317	ESSLEDspot 8W 720lm GU10 830 120D ND RCA	-	75 °C
929002093417	ESSLEDspot 8W 720lm GU10 840 120D ND RCA	-	75 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
929002065602	CorePro LEDspot 3-35W GU10 840 36D DIM	Only with specific dimmers
929002068202	CorePro LEDspot 3-35W GU10 830 36D DIM	Only with specific dimmers
929002068299	CoreProLEDspot 3-35W GU10 830 36D DIM UK	Yes
929002495802	CorePro LEDspot 3-35W GU10 827 36D DIM	Only with specific dimmers
929002495902	CorePro LEDspot 4-50W GU10 827 36D DIM	Only with specific dimmers
929002495999	CoreProLEDspot 4-50W GU10 827 36D DIM UK	Yes
929003562499	CoreProLEDspot 4-50W GU10 865 36D DIM UK	Only with specific dimmers
929001215232	Corepro LEDspot 4.6-50W GU10 827 36D	No
929001215252	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	No
929001215268	Corepro LEDspot 4.6-50W GU10 827 36D UK	No
929001217532	Corepro LEDspot 2.7-25W GU10 827 36D	No
929001217862	Corepro LEDspot 3.5-35W GU10 827 36D	No
929001217897	Corepro LEDspot 3.5-35W GU10 827 36D UK	No
929002981202	Corepro LEDspot 550lm GU10 830 120D	No
929002981302	Corepro LEDspot 550lm GU10 840 120D	No
929002981402	Corepro LEDspot 550lm GU10 865 120D	No
929002065802	CorePro LEDspot 4-50W GU10 840 36D DIM	Only with specific dimmers
929002065899	CoreProLEDspot 4-50W GU10 840 36D DIM UK	Yes
929002068302	CorePro LEDspot 4-50W GU10 830 36D DIM	Only with specific dimmers
929002068399	CoreProLEDspot 4-50W GU10 830 36D DIM UK	Yes
929002981002	CorePro LEDspot 4.9-65W GU10 830 36D ND	No
929002981102	CorePro LEDspot 4.9-65W GU10 840 36D ND	No

Order Code	Full Product Name	Dimmable
929001217602	Corepro LEDspot 2.7-25W GU10 830 36D	No
929001217702	Corepro LEDspot 2.7-25W GU10 840 36D	No
929001217902	Corepro LEDspot 3.5-35W GU10 830 36D	No
929001217999	Corepro LEDspot 3.5-35W GU10 830 36D UK	No
929001218002	Corepro LEDspot 3.5-35W GU10 840 36D	No
929001218099	Corepro LEDspot 3.5-35W GU10 840 36D UK	No
929001218102	Corepro LEDspot 4.6-50W GU10 830 36D	No
929001218199	Corepro LEDspot 4.6-50W GU10 830 36D UK	No
929001218202	Corepro LEDspot 4.6-50W GU10 840 36D	No
929001218299	Corepro LEDspot 4.6-50W GU10 840 36D UK	No
929001218302	Corepro LEDspot 4.6-50W GU10 865 36D	No
929001218308	Essential LED 4.6-50W GU10 865 36D	No
929001218399	Corepro LEDspot 4.6-50W GU10 865 36D UK	No
929003132390	LEDspot GU10 50W 830 36D 6CT	No
929002965587	ESS LEDspot 6W 640lm E14 R50 827	No
929002965687	ESS LEDspot 6W 640lm E14 R50 840	No
929002965787	ESS LEDspot 6W 640lm E14 R50 865	No
929002965887	ESS LEDspot 9W 980lm E27 R63 827	No
929002965987	ESS LEDspot 9W 980lm E27 R63 840	No
929002966087	ESS LEDspot 9W 980lm E27 R63 865	No
929002966187	ESS LEDspot 10W 1150lm E27 R80 827	No
929002966287	ESS LEDspot 10W 1150lm E27 R80 840	No
929002966387	ESS LEDspot 10W 1150lm E27 R80 865	No
929002466702	Corepro LEDspot 670lm GU10 830 60D	No
929002466802	Corepro LEDspot 730lm GU10 840 60D	No
929001372017	ESSLEDspot 6W 500lm GU10 827 120D ND RCA	No
929002093317	ESSLEDspot 8W 720lm GU10 830 120D ND RCA	No
929002093417	ESSLEDspot 8W 720lm GU10 840 120D ND RCA	No

Mechanical and Housing

CorePro LEDspot MV

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929002065602	CorePro LEDspot 3-35W GU10 840 36D DIM	-	PAR16
929002068202	CorePro LEDspot 3-35W GU10 830 36D DIM	-	PAR16
929002068299	CoreProLEDspot 3-35W GU10 830 36D DIM UK	-	PAR16
929002495802	CorePro LEDspot 3-35W GU10 827 36D DIM	-	PAR16
929002495902	CorePro LEDspot 4-50W GU10 827 36D DIM	-	PAR16
929002495999	CoreProLEDspot 4-50W GU10 827 36D DIM UK	-	PAR16
929003562499	CoreProLEDspot 4-50W GU10 865 36D DIM UK	Clear	PAR16
929001215232	Corepro LEDspot 4.6-50W GU10 827 36D	-	PAR16
929001215252	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	-	PAR16
929001215268	Corepro LEDspot 4.6-50W GU10 827 36D UK	-	PAR16
929001217532	Corepro LEDspot 2.7-25W GU10 827 36D	-	PAR16
929001217862	Corepro LEDspot 3.5-35W GU10 827 36D	-	PAR16
929001217897	Corepro LEDspot 3.5-35W GU10 827 36D UK	-	PAR16
929002981202	Corepro LEDspot 550lm GU10 830 120D	-	PAR16
929002981302	Corepro LEDspot 550lm GU10 840 120D	-	PAR16
929002981402	Corepro LEDspot 550lm GU10 865 120D	-	PAR16
929002065802	CorePro LEDspot 4-50W GU10 840 36D DIM	-	PAR16
929002065899	CoreProLEDspot 4-50W GU10 840 36D DIM UK	-	PAR16
929002068302	CorePro LEDspot 4-50W GU10 830 36D DIM	-	PAR16
929002068399	CoreProLEDspot 4-50W GU10 830 36D DIM UK	-	PAR16
929002981002	CorePro LEDspot 4.9-65W GU10 830 36D ND	-	PAR16
929002981102	CorePro LEDspot 4.9-65W GU10 840 36D ND	-	PAR16
929001217602	Corepro LEDspot 2.7-25W GU10 830 36D	-	PAR16
929001217702	Corepro LEDspot 2.7-25W GU10 840 36D	-	PAR16

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929001217902	Corepro LEDspot 3.5-35W GU10 830 36D	-	PAR16
929001217999	Corepro LEDspot 3.5-35W GU10 830 36D UK	-	PAR16
929001218002	Corepro LEDspot 3.5-35W GU10 840 36D	-	PAR16
929001218099	Corepro LEDspot 3.5-35W GU10 840 36D UK	-	PAR16
929001218102	Corepro LEDspot 4.6-50W GU10 830 36D	-	PAR16
929001218199	Corepro LEDspot 4.6-50W GU10 830 36D UK	-	PAR16
929001218202	Corepro LEDspot 4.6-50W GU10 840 36D	-	PAR16
929001218299	Corepro LEDspot 4.6-50W GU10 840 36D UK	-	PAR16
929001218302	Corepro LEDspot 4.6-50W GU10 865 36D	-	PAR16
929001218308	Essential LED 4.6-50W GU10 865 36D	Clear	PAR16
929001218399	Corepro LEDspot 4.6-50W GU10 865 36D UK	-	PAR16
929003132390	LEDspot GU10 50W 830 36D 6CT	-	PAR16
929002965587	ESS LEDspot 6W 640lm E14 R50 827	Frosted	R50
929002965687	ESS LEDspot 6W 640lm E14 R50 840	Frosted	R50
929002965787	ESS LEDspot 6W 640lm E14 R50 865	Frosted	R50
929002965887	ESS LEDspot 9W 980lm E27 R63 827	Frosted	R63
929002965987	ESS LEDspot 9W 980lm E27 R63 840	Frosted	R63
929002966087	ESS LEDspot 9W 980lm E27 R63 865	Frosted	R63
929002966187	ESS LEDspot 10W 1150lm E27 R80 827	Frosted	R80
929002966287	ESS LEDspot 10W 1150lm E27 R80 840	Frosted	R80
929002966387	ESS LEDspot 10W 1150lm E27 R80 865	Frosted	R80
929002466702	Corepro LEDspot 670lm GU10 830 60D	-	PAR16
929002466802	Corepro LEDspot 730lm GU10 840 60D	-	PAR16
929001372017	ESSLEDspot 6W 500lm GU10 827 120D ND RCA	-	PAR16
929002093317	ESSLEDspot 8W 720lm GU10 830 120D ND RCA	-	PAR16
929002093417	ESSLEDspot 8W 720lm GU10 840 120D ND RCA	-	PAR16



Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929002065602	CorePro LEDspot 3-35W GU10 840 36D DIM	3 kWh
929002068202	CorePro LEDspot 3-35W GU10 830 36D DIM	3 kWh
929002068299	CoreProLEDspot 3-35W GU10 830 36D DIM UK	3 kWh
929002495802	CorePro LEDspot 3-35W GU10 827 36D DIM	3 kWh
929002495902	CorePro LEDspot 4-50W GU10 827 36D DIM	4 kWh
929002495999	CoreProLEDspot 4-50W GU10 827 36D DIM UK	4 kWh
929003562499	CoreProLEDspot 4-50W GU10 865 36D DIM UK	4 kWh
929001215232	Corepro LEDspot 4.6-50W GU10 827 36D	5 kWh
929001215252	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	5 kWh
929001215268	Corepro LEDspot 4.6-50W GU10 827 36D UK	5 kWh
929001217532	Corepro LEDspot 2.7-25W GU10 827 36D	3 kWh
929001217862	Corepro LEDspot 3.5-35W GU10 827 36D	4 kWh
929001217897	Corepro LEDspot 3.5-35W GU10 827 36D UK	4 kWh
929002981202	Corepro LEDspot 550lm GU10 830 120D	5 kWh

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929002981302	Corepro LEDspot 550lm GU10 840 120D	5 kWh
929002981402	Corepro LEDspot 550lm GU10 865 120D	5 kWh
929002065802	CorePro LEDspot 4-50W GU10 840 36D DIM	4 kWh
929002065899	CoreProLEDspot 4-50W GU10 840 36D DIM UK	4 kWh
929002068302	CorePro LEDspot 4-50W GU10 830 36D DIM	4 kWh
929002068399	CoreProLEDspot 4-50W GU10 830 36D DIM UK	4 kWh
929002981002	CorePro LEDspot 4.9-65W GU10 830 36D ND	5 kWh
929002981102	CorePro LEDspot 4.9-65W GU10 840 36D ND	5 kWh
929001217602	Corepro LEDspot 2.7-25W GU10 830 36D	3 kWh
929001217702	Corepro LEDspot 2.7-25W GU10 840 36D	3 kWh
929001217902	Corepro LEDspot 3.5-35W GU10 830 36D	4 kWh
929001217999	Corepro LEDspot 3.5-35W GU10 830 36D UK	4 kWh
929001218002	Corepro LEDspot 3.5-35W GU10 840 36D	4 kWh
929001218099	Corepro LEDspot 3.5-35W GU10 840 36D UK	4 kWh
929001218102	Corepro LEDspot 4.6-50W GU10 830 36D	5 kWh






CorePro LEDspot MV

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929001218199	Corepro LEDspot 4.6-50W GU10 830 36D UK	5 kWh
929001218202	Corepro LEDspot 4.6-50W GU10 840 36D	5 kWh
929001218299	Corepro LEDspot 4.6-50W GU10 840 36D UK	5 kWh
929001218302	Corepro LEDspot 4.6-50W GU10 865 36D	5 kWh
929001218308	Essential LED 4.6-50W GU10 865 36D	-
929001218399	Corepro LEDspot 4.6-50W GU10 865 36D UK	5 kWh
929003132390	LEDspot GU10 50W 830 36D 6CT	5 kWh
929002965587	ESS LEDspot 6W 640lm E14 R50 827	6 kWh
929002965687	ESS LEDspot 6W 640lm E14 R50 840	6 kWh
929002965787	ESS LEDspot 6W 640lm E14 R50 865	6 kWh
929002965887	ESS LEDspot 9W 980lm E27 R63 827	9 kWh
929002965987	ESS LEDspot 9W 980lm E27 R63 840	9 kWh
929002966087	ESS LEDspot 9W 980lm E27 R63 865	9 kWh
929002966187	ESS LEDspot 10W 1150lm E27 R80 827	10 kWh
929002966287	ESS LEDspot 10W 1150lm E27 R80 840	10 kWh
929002966387	ESS LEDspot 10W 1150lm E27 R80 865	10 kWh
929002466702	Corepro LEDspot 670lm GU10 830 60D	7 kWh
929002466802	Corepro LEDspot 730lm GU10 840 60D	7 kWh
929001372017	ESSLEDspot 6W 500lm GU10 827 120D ND RCA	6 kWh
929002093317	ESSLEDspot 8W 720lm GU10 830 120D ND RCA	8 kWh
929002093417	ESSLEDspot 8W 720lm GU10 840 120D ND RCA	8 kWh













90°











60°




CorePro LEDspot MV




CorePro LEDspot MV




CorePro LEDspot MV




Accent Diagrams




Accent Diagram - CorePro LEDspot 4.9-65W
GU10 830 36D ND




Accent Diagram - CorePro LEDspot 4-50W GU10
865 36D DIM UK




Accent Diagram - CorePro LEDspot 2.7-25W
GU10 827 36D




Accent Diagram - CorePro LEDspot 3.5-35W
GU10 827 36D UK




Accent Diagram - CorePro LEDspot 4.6-50W
GU10 827 36D 5CT




Accent Diagram - CorePro LEDspot 2.7-25W
GU10 830 36D



Accent Diagram - CorePro LEDspot 3.5-35W
GU10 830 36D UK




Accent Diagram - CorePro LEDspot 4.6-50W
GU10 830 36D




Accent Diagram - CorePro LEDspot 4-50W
GU10 827 36D DIM

CorePro LEDspot MV


Accent Diagrams




Accent Diagram - CorePro LEDspot 4-50W
GU10 840 36D DIM




Accent Diagram - CorePro LEDspot 4-50W GU10
830 36D DIM UK




Accent Diagram - CorePro LEDspot 3-35W GU10
830 36D DIM UK




Accent Diagram - CorePro LEDspot 3-35W GU10
840 36D DIM




Accent Diagram - CorePro LEDspot 730lm GU10
840 60D




Accent Diagram - CorePro LEDspot 670lm GU10
830 60D



Accent Diagram - LEDspot GU10 50W 830 36D
6CT




Accent Diagram - CorePro LEDspot 3-35W GU10
827 36D DIM




Accent Diagram - CorePro LEDspot 4.9-65W
GU10 840 36D ND


Beam Diagrams




Beam diagram - CorePro LEDspot 3-35W GU10 840 36D DIM




Beam diagram - CorePro LEDspot 4.9-65W GU10 840 36D ND




Beam diagram - CorePro LEDspot 2.7-25W GU10 827 36D




Beam diagram - CorePro LEDspot 3.5-35W GU10 827 36D UK




Beam diagram - CorePro LEDspot 4.6-50W GU10 827 36D 5CT




Beam diagram - CorePro LEDspot 2.7-25W GU10 830 36D



Beam diagram - CorePro LEDspot 3.5-35W GU10 830 36D UK




Beam diagram - CorePro LEDspot 4.6-50W GU10 830 36D




Beam diagram - CorePro LEDspot 4-50W GU10 830 36D DIM UK


Beam Diagrams




Beam diagram - CorePro LEDspot 4-50W GU10 840 36D DIM




Beam diagram - CorePro LEDspot 730lm GU10 840 60D




Beam diagram - CorePro LEDspot 3-35W GU10 830 36D DIM UK




Beam diagram - LEDspot GU10 50W 830 36D 6CT




Beam diagram - CorePro LEDspot 4-50W GU10 827 36D DIM




Beam diagram - CorePro LEDspot 3-35W GU10 827 36D DIM



Beam diagram - CorePro LEDspot 4.9-65W GU10 830 36D ND



Beam diagram - CorePro LEDspot 670lm GU10 830 60D



Beam diagram - CorePro LEDspot 4-50W GU10 865 36D DIM UK

CorePro LEDspot MV

