



LuxSpace Accent Mini – The smallest recessed spotlights for retail and hospitality

LuxSpace Accent Mini

Retailers are increasingly having to contend with rising energy prices. At the same time, they need to retain the quality of light they are used to, flexibility in architectural integration, and the right light effects to catch the customer's eye. Last but not least, they need future-proof solutions that will enable them to implement differentiating concepts in their store. Delivering high-quality light, punch in the beam and outstanding luminous efficacy, LuxSpace Accent is the ideal energy-efficient solution for today's demanding retail environments, covering a wide variety of lighting applications

Benefits

- Attract shoppers with high-quality light
- Luminaire design blends discreetly into the store
- Good energy performance, matching CDM Elite while offering much longer lifetime and payback of the Total Cost of Ownership within three years

Features

- Choice of color temperatures: 2700, 3000 and 4000 K
- Narrow, medium, wide, and very wide beams available
- Passive cooling in all versions of the range
- Dimmable versions
- Through-wiring options

LuxSpace Accent Mini

Application

- Retail: fashion and food stores
- Hospitality

