



# Luminous textile: packaged system - bring spaces alive

## Luminous textile panels - packaged system

Many business customers are looking for a lighting solution that will enable them to express emotion, make a design statement, and bring spaces alive. Luminous textile with Kvadrat Soft Cells seamlessly integrates multi-colored LEDs into beautiful fabric panels that also soften sound. It is a concept that gives you endless ways to play with color, movement, texture and light.

### Benefits

- Create a different mood at the touch of a button
- Easy to install (all you need is a wall and two mains sockets)
- Easy to control (free software to add dynamic content and DiscoverMe LTP app)

### Features

- Soft touch: Kvadrat design textiles
- Soft fascination: low-resolution dynamic content
- Soft sound: acoustic properties
- Standard content library available at [www.largeluminoussurfaces.com/content](http://www.largeluminoussurfaces.com/content)

### Application

- Ambient lighting for:
  - Retail stores (flagships)
  - Reception areas (hospitality)
  - Offices

### Specifications

Type	LP700W	Light source	Replaceable LED module
------	--------	--------------	------------------------

## Luminous textile panels - packaged system

<b>Power</b>	55 W/m	<b>Material</b>	Kvadrat textile Toto 202
<b>Luminous flux</b>	500 lm/m		Frame: aluminum
<b>Median useful life L70B50</b>	60,000 hours	<b>Color</b>	Textile: off white
<b>Average ambient temperature</b>	+25 °C		Frame: aluminum
<b>Operating temperature range</b>	+5 to +35 °C	<b>Connection</b>	IEC for power input and throughput, RJ45 for data
<b>Driver</b>	Built-in	<b>Installation</b>	4 panels 1200 x 2520 mm, portrait or landscape
<b>Mains voltage</b>	100-240 V		Wall hooks and magnets included
<b>Controls system input</b>	Integrated		Mains through-wiring possible
		<b>Remarks</b>	Content playback controller integrated
			Control via free DiscoverMe LTP app

## Versions



## Product details



Driver box mounted on rear of panel

