



942 - adding elegance and improved visibility to the low level environment

942 Horizontal Aisle Light

For applications requiring higher output levels and increased spacings, 942 luminaires offer a wide choice of faceplate designs and lumen packages. These horizontal aisle lights accept sources up to 100W H.I.D.

Benefits

- Protected against moisture, dust and insects
- Low-glare illumination, free from streaks or striations
- Quick installation and maintenance
- Eliminates potential for misapplication
- Provides additional design flexibility

Features

- Sealed and gasketed
- Specular Alzak hammertone reflectors
- Firmly secured reflector and electrical assembly
- Available for installation in all types of wall construction

Application

- Walkways

942 Horizontal Aisle Light

Versions

