



ATR74 - enhancing your project's unique style

Pole (ATR74)

Made from tapered 7" to 4" (178 by 102 mm) round aluminum shaft welded top and bottom to a cast-aluminum anchor plate. After tapering and welding, the entire shaft assembly is heat-treated to T6 temper. A 4" by 7" (102 by 178 mm) maintenance opening is complete with cover and copper ground lug [~LT~a href="http://www.lumec.com/Lumec3Dv3/home/index_en.php" target="_blank"~GT~~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~~LT~/a~GT~](http://www.lumec.com/Lumec3Dv3/home/index_en.php)

Benefits

- Built to withstand harsh environmental conditions
- Superior corrosion resistance
- Optimal strength and durability

Features

- Round tapered
- Aluminum construction
- Available in various heights ranging from 20' to 25'

Application

- Bridges, Monuments, Facades
- Road and Street

Pole (ATR74)

Versions

