



Wide range of performance downlights

5" Lytecaster Reflector Trim

Step Baffle Wall Washer provides a high intensity, smooth wash of light up to the ceiling line. Dual reflector optics assure effective output with economical light sources while the aluminum step baffle reduces glare.

Benefits

- All reflectors are self-flanged to eliminate light leaks
- Anodized reflectors control light rays to avoid scatter, providing more usable light
- Light source sits high up to collect and redirect light from the lamp
- Unitized Optics provides a forgiving installation that assures full reflector output at all times

Features

- Snap-on socket assures correct lamp alignment, brackets adjust for different lamp sizes
- Lamp is recessed above the ceiling line to cut off distracting brightness
- Wall wash, sloped ceiling, eye ball trims available

Application

- Residential
- Hospitality

5" Lytecaster Reflector Trim

Versions



5" Lytecaster Reflector Trim

Versions

