



AH Overbed Light

4', 2 Lamp F32T8

4', 2 Lamp F32T8

Wall mounted luminaire suitable for hospitals and other health care facilities it has separate lamp compartments for segregated uplight and downlight

Product data

| General Information | |
|-------------------------------|-----------------|
| Lamp Source Code | FLU |
| Lamp Watts | 32 |
| Lamp Envelope Code | T-8 |
| Number of Lamps | 2 |
| Photometric Distribution Type | General Diffuse |
| Mounting | Surface Wall |
| Operating and Electrical | |
| Luminaire Input Watts | 56 |
| Voltages | 120/277/347 V |
| Mechanical and Housing | |
| Fixture Size | 48 in |

| Shape | Linear |
|----------------------------|------------------|
| Product Data | |
| Order product name | 4', 2 Lamp F32T8 |
| Commercial Code | AH232-1/2-EB |
| Order code | AH232-1/2-EB |
| Catalog Number Description | 4', 2 Lamp F32T8 |
| Service / Spec Smart | - |
| Material Nr. (12NC) | DAY00000064 |