



Arioso Recessed LED

2x2, 3800 Nominal Delivered Lumens, 4000K, Frosted Acrylic Lens

2x2, 3800 Nominal Delivered Lumens, 4000K, Frosted Acrylic Lens

The Philips Day-Brite / Philips CFI Arioso Recessed LED offers standard-setting efficiency without aesthetic compromise. These LED luminaires combine state-of-the-art, flexible and globally- recognized LED lighting platforms with proven Arioso optical combinations.

Product data

General Information

Lamp Source Code	LED
Color Temperature	4000K
CRI	80
Photometric Distribution Type	Direct
Mounting	Recessed

Operating and Electrical

Luminaire Input Watts	40
-----------------------	----

Mechanical and Housing

Fixture Size	2 ft x 2 ft
Shape	Square

Initial Performance (IEC Compliant)

Luminaire Lumens	3800
------------------	------

Product Data

Order product name	2x2, 3800 Nominal Delivered Lumens, 4000K, Frosted Acrylic Lens
Commercial Code	2AVEG38L840-2-ACR
Order code	2AVEG38L840-2-ACR
Catalog Number Description	2x2, 3800 Nominal Delivered Lumens, 4000K, Frosted Acrylic Lens
Service / Spec Smart	-
Material Nr. (12NC)	DAY00000446