



Industrial Docklight

42" Adjustable Arm, 150w MAX. PAR 38 or R40 Lamp

42" Adjustable Arm, 150w MAX. PAR 38 or R40 Lamp

Rugged flexibility combined with incredible energy savings is probably the best way to describe this beautifully designed Dock Light. Incorporating a robust die cast exterior, this dock light is designed to withstand the rigorous demands of shipping and receiving areas.

Product data

General Information	
Lamp Source Code	INC
Lamp Watts	150
Number of Lamps	1
Mounting	Surface Wall
Operating and Electrical	
Voltages	120 V

Product Data	
Order product name	42" Adjustable Arm, 150w MAX. PAR 38 or R40 Lamp
Commercial Code	ID1L42-120
Order code	ID1L42-120
Catalog Number Description	42" Adjustable Arm, 150w MAX. PAR 38 or R40 Lamp
Service / Spec Smart	Spec Smart (10 Days) Canada
Material Nr. (12NC)	DAY00003033