



LBD Low Bay

1 Lamp 400wMH, Acrylic Lens

1 Lamp 400wMH, Acrylic Lens

The LBD Low Bay Luminaire offers the highest efficiency for general purpose industrial lighting; of any low bay manufactured in the U.S. It is the finest fixture made for mounting heights of 30' and below.

Product data

General Information	
Lamp Source Code	MH
Lamp Watts	400
Lamp Envelope Code	BT/ED/E-37
Number of Lamps	1
Photometric Distribution Type	Direct
Mounting	Suspended
Operating and Electrical	
Luminaire Input Watts	458
Voltages	120/208/240/277/347/480 V
Mechanical and Housing	
Fixture Size	28 in

Shape	Round
Product Data	
Order product name	1 Lamp 400wMH, Acrylic Lens
Commercial Code	LBD400M-BRA
Order code	LBD400M-BRA
Catalog Number Description	1 Lamp 400wMH, Acrylic Lens
Service / Spec Smart	-
Material Nr. (12NC)	DAY00003456