



Kleenseal 100 Recessed Cleanroom LED

2x4, 11000 Nominal Delivered Lumens, 80 CRI, 4000K, .125" Prismatic Acrylic, Wet Location, Inset Doorframe w/Captive Screws

2x4, 11000 Nominal Delivered Lumens, 80 CRI, 4000K, .125" Prismatic Acrylic, Wet Location, Inset Doorframe w/Captive Screws

The Kleenseal KTR 100 is a cleanroom luminaire well suited for laboratories, fuel storage areas and dirty areas such as locker rooms. Ideal for Class 100-100,000 cleanrooms.

Product data

General Information	
Lamp Source Code	LED
Color Temperature	4000K
CRI	80
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	UNIV V
Mechanical and Housing	
Fixture Size	2 ft x 4 ft
Shape	Rectangular
Initial Performance (IEC Compliant)	
Luminaire Lumens	11000

Product Data	
Order product name	2x4, 11000 Nominal Delivered Lumens, 80 CRI, 4000K, .125" Prismatic Acrylic, Wet Location, Inset Doorframe w/Captive Screws
Commercial Code	K124110L840G-6AP3
Order code	K124110L840G-6AP3
Catalog Number Description	2x4, 11000 Nominal Delivered Lumens, 80 CRI, 4000K, .125" Prismatic Acrylic, Wet Location, Inset Doorframe w/Captive Screws
Service / Spec Smart	-
Material Nr. (12NC)	DAY00008916

Kleenseal 100 Recessed Cleanroom LED

