



Arano TCS640

TCS640 3x14W/830 HFP M2 WH

ARANO, 3, 14 W, 830 warm white, HF Performer, Matt mirror ribbed lamellae louver, White

Arano is a range of luminaires for TL5 fluorescent lamps and LED light sources, featuring Philips' micro-optics. The patented micro-optic with 3-D lamellae combines a miniaturist design with optimum performance in terms of light distribution, visual comfort and efficiency. And it is fully compliant with the current norm for indoor working places (EN12464-1). Surface-mounted, suspended, free-standing and wall-mounted versions are available – some with direct/indirect lighting – to create a bright, welcoming ambience. Multiple Arano luminaires can be linked to create line arrangements.

Product data

General Information		Optical cover type	
Lamp family code	TL5 [TL5]		-
Gear	HFP [HF Performer]	Operating and Electrical	
Product family code	TCS640 [ARANO]	Power Consumption	14 W
Embedded control	-	Cable	-
CE mark	Yes	Mechanical and Housing	
Flammability mark	For mounting on normally flammable surfaces	Housing Color	White
ENEC mark	ENEC mark	Approval and Application	
Glow-wire test	Temperature 960 °C, duration 5 s	Ingress protection code	IP20 [Finger-protected]
Light Technical		Protection class IEC	Safety class I
Number of light sources	3		
Light source color	830 warm white		
Optic type	Matt mirror ribbed lamellae louver		

Arano TCS640

Application Conditions

Suitable for random switching Not applicable

Product Data

Order product name TCS640 3x14W/830 HFP M2 WH
Full product name TCS640 3x14W/830 HFP M2 WH
Full product code 871155974923500
Order code 910501265203

Material Nr. (12NC) 910501265203

Numerator - Quantity Per Pack 1

EAN/UPC - Product/Case 8711559749235

Numerator - Packs per outer box 1

EAN/UPC - Case 8711559749235

Dimensional drawing

