



Gondola

FWG251 2xPL-C/4P26W HF WH

2, MASTER PL-C 4 Pin, 26 W, Electronic high-frequency, White

Gondola is a waterproof and shock- and vandal-resistant luminaire with a fresh, appealing design. Its highly efficient HF driver significantly reduces energy consumption, while the long lifetime of the light source means that maintenance costs are kept to a minimum. Gondola can be wall- or ceiling-mounted and is ideal for efficient illumination of areas such as stairwells and corridors.

Product data

General Information	
Lamp family code	PL-C/4P [MASTER PL-C 4 Pin]
Cap-Base	G24Q-3 [G24q-3]
Gear	HF [Electronic high-frequency]
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 5 s

Light Technical	
Number of light sources	2

Operating and Electrical	
Input Voltage	220 to 240 V
Power Consumption	26 W

Mechanical and Housing	
Housing Color	White

Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]

Mech. impact protection code	IK10 [20 J vandal-resistant]
Protection class IEC	Safety class I

Application Conditions	
Suitable for random switching	Not applicable

Product Data	
Order product name	FWG251 2xPL-C/4P26W HF WH
Full product name	FWG251 2xPL-C/4P26W HF WH
Full product code	87179438922899
Order code	910503668418
Material Nr. (12NC)	910503668418
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943892228
Numerator - Packs per outer box	4
EAN/UPC - Case	8717943892563

Gondola

Dimensional drawing

