



# CoreLine Malaga LED

## BRP101 LED37/740 DM FU

CoreLine Malaga LED, Street light, 29.5 W, 3054 lm, 4000 K, CRI70, Distribution medium, Safety class I, IP65, FU, SRG4-4

The Philips CoreLine Malaga LED family consists of two sizes for urban street lighting. Both use a Philips LED engine as a light source and a Philips Xitanium driver – a combination that results in energy savings of 50%. CoreLine Malaga LED has been designed to be as efficient as possible. It offers the same performance as the SON-T 50, 70, 100 and 150W luminaires it replaces, providing the right amount of light in the right place. Furthermore, as the LED light engine in CoreLine Malaga LED will last for the lifetime of the luminaire, it will return your investment simply by saving on the multiple lamp replacements required with SON-T. With its extended gland feature, the CoreLine Malaga LED luminaire is easy to install with no need to open the luminaire to connect the power cable. At the same time, the flat glass cover can be removed to allow access to the driver for maintenance, if required. Special versions of Malaga lighting are available with extra options. However, these specials are manufactured to order only, and have a longer delivery time. The options include: Wide beam (DW) optic, additional surge protection device (10kV), Marine Salt Protection (MSP) paint finish, Micro Mini Pro photocell 35 Lux, a built-in (glass) 6A fuse, and a 3-meter external flying lead cable (H07RN-F). Not all these options can always be combined with each other. For more advice, please consult your Philips partner.

### Product data

General Information		Product family code	
Lamp family code	LED37 [LED module 3700 lm]	BRP101 [CoreLine Malaga LED small]	
Light source replaceable	No	Lighting Technology	
Number of gear units	1 unit	LED	
Driver included	Yes	Value ladder	
Light source engine type	LED	Performance	
		CE mark	
		Yes	
		Warranty period	
		5 years	
		Flammability mark	
		-	

## CoreLine Malaga LED

ENEC mark	ENEC mark
EU RoHS compliant	Yes

### Light Technical

Upward light output ratio	0
Luminous Flux	3,054 lm
Standard tilt angle posttop	-
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	103 lm/W
Color rendering index (CRI)	70
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	-
Optic type outdoor	Distribution medium

### Operating and Electrical

Input Voltage	200-220 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	N/A W
Average CLO power consumption	N/A W
End CLO power consumption	N/A W
Inrush current	7.1 A
Inrush time	61.2 ms
Power Consumption	29.5 W
Power Factor (Fraction)	0.98
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	11

### Temperature

Ambient temperature range	-40 to +35 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

### Mechanical and Housing

Housing Material	Aluminum die-cast
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	Tempered glass
Fixation material	Aluminum
Housing Color	Gray
Mounting device	Universal for diameter 42 to 60 mm adjustable
Optical cover shape	Flat

Optical cover finish	Clear
Overall length	333 mm
Overall width	197 mm
Overall height	78 mm
Effective projected area	0.016478 m²
Dimensions (Height x Width x Depth)	78 x 197 x 333 mm

### Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 4 kV differential mode and 4 kV common mode
Sustainability rating	-
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 1 @200mm to EN62778

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.41, 0.39) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

### Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.05 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L70

### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable

### Product Data

Order product name	BRP101 LED37/740 DM FU
Full product name	BRP101 LED37/740 DM FU
Full product code	871869944820200
Order code	910925865553
Material Nr. (12NC)	910925865553
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699448202
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699448202

## CoreLine Malaga LED

### Dimensional drawing

