



Luminous textile panels - packaged system

LP700W LUMINOUSTEXTILE 4TTO202L2520W1200

LUMINOUS TEXTILE PANEL - Luminous textile panel 4 pcs, textile Toto 202, length 2520 mm, width 1200 mm

Many business customers are looking for a lighting solution that will enable them to express emotion, make a design statement, and bring spaces alive. Luminous textile with Kvadrat Soft Cells seamlessly integrates multi-colored LEDs into beautiful fabric panels that also soften sound. It is a concept that gives you endless ways to play with color, movement, texture and light.

Product data

| General Information | |
|-------------------------------|---|
| Number of light sources | 1 pc |
| Light source color | Red, green and blue |
| Light source replaceable | No |
| Driver/power unit/transformer | Power supply unit |
| Driver included | Yes |
| Connection | AC power connector C13 |
| Protection class IEC | Safety class I |
| Ready-to-install | Ready-to-install |
| Type description | Luminous textile panel 4 pcs, textile Toto 202, length 2520 mm, width 1200 mm |
| CE mark | CE mark |

| ENEC mark | - |
|--------------------------|-----------------------------------|
| UL mark | UL mark |
| Packaging configuration | 4 pieces |
| Product family code | LP700W [LUMINOUS TEXTILE PANEL] |
| Operating and Electrical | |
| Input Voltage | 100 to 240 V |
| Input Frequency | 50 to 60 Hz |
| Controls and Dimming | |
| Dimmable | No |

Luminous textile panels - packaged system

Mechanical and Housing

| | |
|--------------------|----------|
| Housing Material | Aluminum |
| Gear tray material | Steel |
| Color | Aluminum |

Approval and Application

| | |
|------------------------------|-----------------------|
| Ingress protection code | IP00 [No protection] |
| Mech. impact protection code | IK00 [No protection] |

Initial Performance (IEC Compliant)

| | |
|-------------------------------------|---------|
| Initial luminous flux (system flux) | 6000 lm |
| Initial LED luminaire efficacy | 9 lm/W |
| Initial input power | 660 W |
| Power consumption tolerance | +/-10% |

Application Conditions

| | |
|---------------------------|--------------|
| Ambient temperature range | +5 to +35 °C |
|---------------------------|--------------|

| | |
|-------------------------------|----|
| Suitable for random switching | No |
|-------------------------------|----|

Product Data

| | |
|---------------------------------|--|
| Full product code | 871869607041300 |
| Order product name | LP700W LUMINOUSTEXTILE 4TTO202L2520W1200 |
| EAN/UPC - Product | 8718696070413 |
| Order code | 912000000420 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |
| Material Nr. (12NC) | 912000000420 |
| Net Weight (Piece) | 237.000 kg |

