



F-can (72C)

F-CAN HID MH BAL 175W M137/152 120/277V FCAN

The Philips Advance line of F-can HID ballasts comes in two dual-voltage configurations for the US and Canadian market. Ballasts for these luminaires are most often encased and potted in fluorescent ballast type cans.

Product data

General Information	
ANSI Code	M137-M152(PULSESTART)
Lamp Type	175W MH
Number of Lamps	1 piece/unit
Circuit Type	CWA
Ballast Type	Magnetic HID
Base Model	72C5582
Suitable For Outdoor Use	Yes
Ignitor Catalog Number	Inside Can
Capacitor Catalog Number	Inside Can
Automatic Restart	No
Operating and Electrical	
Input Voltage	120/277 V
Input Frequency	60 Hz
Inp. Current (Open Circuit)	2.15/0.92 A
Input Current (Starting)	0.85/0.36 A
Input Current (Short Circuit)	0.56-0.85/0.24-0.36 A
Secondary Short Circuit Current	1.55-1.9 A
Constant Wattage Deviation	10%
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Nominal Open Circuit Voltage	303 V

Input Current (Operating) (Nom)	1.75/0.75 A A
Input Power (Nom)	205 W
Rated Lamp Watts	175 W
Wiring	
Wire Striplength	0.5 mm
Wire Length by Color	12"
Wire Type	Stranded
Remote Wiring Configuration Allowed	Yes
Max Ballast-Lamp Distance Remote Wiring	50'
Recommended Fuse Value	5/3 A
Mechanical and Housing	
Housing Material	Metal
Housing	F-Can
Housing Dimensions	14.3 x 2.63 x 3.19
Approval and Application	
Open Circuit Voltage Test (Volts)	270-330 V
Approbation Marks	CSA certificate UL certificate RoHS Compliant
Temperature Marking	90°C max. case
UL Recognized	No

F-can (72C)


Hipot Test (1 Minute)	1500 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	A(105°C)
UL Temperature Code	NA

Product Data

Order product name	F-CAN HID MH BAL 175W M137/152 120/277V FCAN
--------------------	---

EAN/UPC - Product	781087112052
Order code	72C5582NP
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	913700501531
Net Weight (Piece)	5.702 kg

Dimensional drawing



MH BAL 175W M137/152 120/277V FCAN

Product	A1	A2	A3	B1	B2	C1	D1
F-CAN HID 72C5582NP	12 in	13.75 in	13.13 in	3.9 in	2.0 in	2.6 in	0.3 in

