



Standard Candle B35 frosted

Stan 40W E27 220-240V B35 FR 1CT/5X10F

Flame-shaped bulb with clear or inside-frosted glass and vacuum- or gas-filled bulb

Product data

| General Information | |
|------------------------|----------------------------------|
| Cap-Base | E27 [E27] |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime | 1,000 hour(s) |
| Rated Lifetime (Hours) | 1,000 hour(s) |
| Lighting Technology | Incandescent |

| Light Technical | |
|-----------------------------|--------|
| Luminous Flux | 390 lm |
| Color rendering index (CRI) | 100 |

| Operating and Electrical | |
|--------------------------|-----------|
| Power Consumption | 40 W |
| Voltage (Nom) | 220-240 V |


| Controls and Dimming | |
|----------------------|-----|
| Dimmable | Yes |

| Mechanical and Housing | |
|------------------------|--------------|
| Bulb Finish | Frosted |
| Bulb Shape | B35 [B 35mm] |

| Product Data | |
|---------------------------------|--|
| Order product name | Stan 40W E27 220-240V B35 FR 1CT/5X10F |
| Full product name | Stan 40W E27 220-240V B35 FR 1CT/5X10F |
| Full product code | 871829112447400 |
| Order code | 921492143301 |
| Material Nr. (12NC) | 921492143301 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500222916 |
| Numerator - Packs per outer box | 50 |
| EAN/UPC - Case | 8718291124498 |

Standard Candle B35 frosted

Dimensional drawing



| Product | D | C (max) |
|--|-------|---------|
| Stan 40W E27 220-240V B35 FR 1CT/5X10F | 35 mm | 96.5 mm |

