



Reflector Colours diam 50/63/80 mm

Refl Col 40W E14 230V NR50 CL-RE 1CT/15

Externally lacquered reflector lamps in various colours for striking indoor lighting effects

Product data

General Information	
Cap-Base	E14 [E14]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Switching Cycle	4,000
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent

Light Technical	
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	100
Luminous Flux in 90° Cone (Rated)	44 lm

Operating and Electrical	
Power Consumption	40.0 W
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Voltage (Nom)	230 V
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb Finish	Clear Red
Bulb Shape	NR50 [NR 50mm]

Approval and Application	
Energy Consumption kWh/1000 h	40 kWh

Product Data	
Order product name	Refl Col 40W E14 230V NR50 CL-RE 1CT/15
Full product name	Refl Col 40W E14 230V NR50 CL-RE 1CT/15
Full product code	871150032806920
Order code	923348944217
Material Nr. (12NC)	923348944217
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500328069
Numerator - Packs per outer box	15
EAN/UPC - Case	8711500343710

Reflector Colours diam 50/63/80 mm

Dimensional drawing



Product	D (max)	C (max)
Refi Col 40W E14 230V NR50 CL-RE 1CT/15	50 mm	87 mm

