



# Reflector Infrared BR40, PAR38

## 100PAR38/HEAT/CL 120V 12/1

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. Philips Infrared lamps are suited for heating and drying in industrial and commercial applications. These incandescent, gas-filled infrared heat lamps come up to full temperature almost immediately, eliminating costly warm-up time. Highly efficient heat generators that produce a minimum of light rays and a high amount of infrared radiation. The BR40 lamp provides a built-in reflector for radiant energy control.

### Product data

General Information	
Cap-Base	E26/50X39 [Skirted Medium Screw (PAR Lamps)]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	5,000 hour(s)
Rated Lifetime (Hours)	5,000 hour(s)
Lighting Technology	Incandescent

Light Technical	
Color Designation	C

Operating and Electrical	
Power Consumption	100 W
Voltage (Nom)	120 V
Voltage (Nom)	120 V

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	PAR38 [PAR 4.75 inch/121mm]

Product Data	
Order product name	100PAR38/HEAT/CL 120V 12/1
Full product name	100PAR38/HEAT/CL 120V 12/1
Full product code	904667722191115
Order code	145508
Material Nr. (12NC)	923800836307
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677221911
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677145502

## Reflector Infrared BR40,PAR38

### Dimensional drawing



Product	D	C (max)	C1 (max)
100PAR38/HEAT/CL 120V 12/1	4-13/16 inch	5-5/16 inch	4-7/8 inch

