



Aluline 37/56

Alu 20W 12V R37 18D CL 1CT/10X5F

Low-voltage halogen burner in specialized aluminum reflector prevents heat in the backlight; bayonet cap for secure fitting

Product data

General Information	
Cap-Base	BA15D [BA15d]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	4,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	4,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Beam Angle (Nom)	18 degree(s)
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	100
Luminous Flux in 90° Cone (Rated)	235 lm
Operating and Electrical	
Power Consumption	20.0 W
Lamp Current (Nom)	1.67 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	12 V
Voltage (Nom)	12 V


Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	R37 [R 37mm]
Approval and Application	
Energy Consumption kWh/1000 h	21 kWh
Product Data	
Order product name	Alu 20W 12V R37 18D CL 1CT/10X5F
Full product name	Alu 20W 12V R37 18D CL 1CT/10X5F
Full product code	871869666675300
Order code	923882817102
Material Nr. (12NC)	923882817102
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696666753
Numerator - Packs per outer box	50
EAN/UPC - Case	8718696666777

Aluline 37/56

Dimensional drawing

Product	D (max)	C (max)
Alu 20W 12V R37 18D CL 1CT/10X5F	38 mm	41 mm

Photometric data



Light Distribution Diagram - Alu 20W 12V R37 18D CL 1CT/10X5F

