



MR16

20MR16/FL36 BAB 50PK

Philips Halogen MR16 lamps provide a bright white light for accent lighting. They make it easy to optimize the look and feel of your brand, your merchandise, and the shoppers experience, with lower operating costs.

Product data

General Information	
Cap-Base	GU5.3 [GU5.3]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	3,000 hour(s)
Rated Lifetime (Hours)	3,000 hour(s)
Lighting Technology	Halogen

Light Technical	
Beam Angle (Nom)	36 degree(s)
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	20.0 W
Lamp Current (Nom)	1.67 A
Starting Time (Nom)	0.0 s
Voltage (Nom)	12 V
Voltage (Nom)	12 V


Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]

Product Data	
Order product name	20MR16/FL36 BAB 50PK
Full product name	20MR16/FL36 BAB 50PK
Order code	378034
Material Nr. (12NC)	924047217122
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677378035
Numerator - Packs per outer box	50
EAN/UPC - Case	50046677378030

MR16

Dimensional drawing



Product	D (max)	C (max)
20MR16/FL36 BAB 50PK	51 mm	46 mm

