



Halogen Classic P45

ClassicHalo 30 28W B22 240V P45 CL 2PF

Philips Halogen Classic light bulbs offer the classical shapes you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.

Product data

General Information	
Cap-Base	B22 [B22]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2.000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2.000 hour(s)
Lighting Technology	Halogen
Light Technical	
Luminous Flux	370 lm
Correlated Color Temperature (Nom)	2800 K
Luminous Efficacy (rated) (Nom)	12.4 lm/W
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	28 W
Lamp Current (Nom)	0.12 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	240 V

Voltage (Nom)	240 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	P45 [P 45mm]
Product Data	
Order product name	ClassicHalo 30 28W B22 240V P45 CL 2PF
Full product name	ClassicHalo 30 28W B22 240V P45 CL 2PF
Full product code	871829121978100
Order code	925648645503
Material Nr. (12NC)	925648645503
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291219781
Numerator - Packs per outer box	100
EAN/UPC - Case	8718291219804

Halogen Classic P45

Dimensional drawing

Product	D (max)	C (max)
ClassicHalo 30 28W B22 240V P45 CL 2PF	46 mm	72.5 mm

