



PLUS T8 High Output

F96T8/TL841/HO/PL ALTO TG

Philips PLUS T8 High Output 8-foot fluorescent lamps reduce the impact on the environment by offering long life and low mercury.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	R17D [R17d (RDC)]
Features	ALTO® Plus

Light Technical	
Color Code	TL841 [CCT of 4100K (841)]
Luminous Flux	8,200 lm
Color Designation	TL841
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	85

Operating and Electrical	
Power Consumption	86 W

Mechanical and Housing	
Bulb Shape	T-8 (T8)

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	4.4 mg

Product Data	
Order product name	F96T8/TL841/HO/PL ALTO TG
Full product name	F96T8/TL841/HO/PL ALTO TG
Order code	409128
Material Nr. (12NC)	927874084107
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677409128
Numerator - Packs per outer box	25
EAN/UPC - Case	50046677409123

PLUS T8 High Output

Dimensional drawing

Product

F96T8/TL841/HO/PL ALTO TG

