



TuffGuard Coated T12

F48T12/CW/HO ALTO TG 15PK

When you select Philips TuffGuard™ Fluorescent lamp with ALTO® lamp technology, you are reducing the impact on the environment, while the coating helps to protect your customers, employees, and reputation. Philips TuffGuard™ fluorescent lamps meet sustainability requirements because they reduce the impact on the environment with low mercury, energy efficiency and long life. The patented green endcaps mean you're using ALTO low-mercury technology. The 16 mils thick coating on TuffGuard™ fluorescent lamps forms a protective seal from end to end and is guaranteed to last the average rated life of the lamp under specific conditions

Warnings and Safety

- All HO lamps recommended for use only in open fixtures.

Product data


General Information		Approval and Application	
Cap-Base	R17D [R17d (RDC)]	Energy Saving Product	Not Applicable
Features	ALTO® (ALTO)	Mercury (Hg) Content (Nom)	3.5 mg
Light Technical		Product Data	
Color Code	33	Order product name	F48T12/CW/HO ALTO TG 15PK
Luminous Flux	4,050 lumen	Order code	927890203309
Color Designation	Cool White (CW)	Numerator - Quantity Per Pack	1
Correlated Color Temperature (Nom)	4100 K	Numerator - Packs per outer box	15
Color rendering index (CRI)	62	Material Nr. (12NC)	927890203309
Operating and Electrical		Full product name	F48T12/CW/HO ALTO TG 15PK
Power Consumption	60 W	EAN/UPC - Case	50046677162967
		EAN/UPC - Product/Case	046677162962
Mechanical and Housing			
Bulb Shape	T-12 (T12)		

TuffGuard Coated T12

Dimensional drawing

Product

F48T12/CW/HO ALTO TG 15PK



T12 Recessed Double Contact

