



# PL-S 2 Pin

## PL-S 9W/827/2P 1CT/25

PL-S is an efficient low-wattage compact fluorescent lamp, typically used for decorative and orientation purposes. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base.

### Product data

General Information	
Cap-Base	G23 [G23]
Life to 50% Failures (Nom)	8,000 h

Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	600 lm
Color Designation	Incandescent White
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	69 lm/W
Color rendering index (CRI)	>80

Operating and Electrical	
Power Consumption	8.6 W
Lamp Current (Nom)	0.170 A
Voltage (Nom)	60 V
Voltage (Nom)	60 V

Controls and Dimming	
Dimmable	No


Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg

Product Data	
Order product name	PL-S 9W/827/2P 1CT/25
Full product name	PL-S 9W/827/2P 1CT/25
Full product code	871150070679900
Order code	927901708265
Material Nr. (12NC)	927901708265
Local order code	PLS9W8272P
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500706799
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500534033


## PL-S 2 Pin

### Dimensional drawing



Product	D (max)	D1 (max)	C (max)
PL-S 9W/827/2P 1CT/25	27.1 mm	13 mm	167.5 mm

### Photometric data



Spectral Power Distribution Colour - PL-S 9W/827/2P 1CT/25

