



# PL-T Triple 4-Pin Base

## PL-T 42W/830/A/4P 1CT/5X10BOX ALTO

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

### Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050


### Product data

General Information		Lamp Current (Nom)	
Cap-Base	GX24q-4		0.320 A
Light Technical		Controls and Dimming	
Color Code	830 [CCT of 3000K]	Dimmable	Yes
Luminous Flux	3,200 lm	Approval and Application	
Color Designation	Warm White (WW)	Mercury (Hg) Content (Nom)	1.4 mg
Correlated Color Temperature (Nom)	3000 K	Product Data	
Luminous Efficacy (Rated) (Min)	80 lm/W	Order product name	PL-T 42W/830/A/4P 1CT/5X10BOX ALTO
Color rendering index (CRI)	>80	Full product name	PL-T 42W/830/A/4P 1CT/5X10BOX ALTO
Operating and Electrical		Order code	149013
Power Consumption	38.0 W	Material Nr. (12NC)	927911483020
		Numerator - Quantity Per Pack	1

# PL-T Triple 4-Pin Base


EAN/UPC - Product/Case	046677149017
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677149012

## Dimensional drawing




Product	D (max)	A (max)	B (max)	C (max)
PL-T 42W/830/A/4P 1CT/5X10BOX ALTO	1-5/8 inch	4-3/4 inch	5-3/4 inch	6-3/8 inch

## Photometric data




Spectral Power Distribution Colour - PL-T 42W/830/A/4P 1CT/5X10BOX ALTO

## Lifetime




Lumen Maintenance Diagram - PL-T 42W/830/A/4P 1CT/5X10BOX ALTO



Life Expectancy Diagram - PL-T 42W/830/A/4P 1CT/5X10BOX ALTO

## PL-T Triple 4-Pin Base

### Lifetime



Life Expectancy Diagram - PL-T 42W/830/A/4P 1CT/5X10BOX ALTO

