



TL Blacklight Blue

F40T12/BLACKLIGHT/48 BLB LF

TL/O8 Blacklight Blue lamps are low-pressure mercury-vapor fluorescent lamps. They have an inner envelope coated with a fluorescent powder that emits long-wave UV radiation to excite luminescence.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050


Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	9,000 hour(s)
Useful Life (Nom)	5,000 hour(s)
Light Technical	
Color Code	108 [08 lead free glass]
Color Designation	Blacklight Blue
Operating and Electrical	
Power Consumption	39 W
Lamp Current (Nom)	0.43 A
Voltage (Nom)	104 V
Voltage (Nom)	104 V
Mechanical and Housing	
Bulb Shape	T38 [T 38mm]

Approval and Application	
Mercury (Hg) Content (Nom)	13.0 mg
UV	
UV-A Radiation 0Hr (IEC)	9.8 W
UV-A Radiation 100Hr (IEC)	9.6 W
Product Data	
Order product name	F40T12/BLACKLIGHT/48 BLB LF
Full product name	F40T12/BLACKLIGHT/48 BLB LF
Order code	157628
Material Nr. (12NC)	928011310821
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677157623
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677157628


TL Blacklight Blue

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
F40T12/ BLACKLIGHT/48 BLB	1-5/8 inch	47-1/4 inch	47-1/2 inch	47-7/16 inch	47-13/16 inch
LF					

Photometric data



Spectral Power Distribution Colour - F40T12/BLACKLIGHT/48 BLB LF

