



MSR Hot Restrike

MSR 200 HR 1CT/4

Thanks to an optimized color temperature and a high color rendering index, the MSR Hot Restrike creates perfect 'daylight' in any condition. Also, the single ended lamp design enables hot re-ignition, which ensures daylight lighting and superb color rendition is always instantly available. They also incorporate the innovative P3 technology, developed by Philips, which allows use at higher temperatures and therefore extends lifetime and consistency of high-quality light output.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	GZY9.5
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	200 hour(s)

Light Technical	
Color Code	- [Not Specified]
Luminous Flux (Min)	12,000 lm
Luminous Flux	15,000 lm
Chromaticity Coordinate X (Nom)	325
Chromaticity Coordinate Y (Nom)	323
Correlated Color Temperature (Nom)	6000 K
Luminous Efficacy (rated) (Nom)	75 lm/W
Color rendering index (CRI)	92
Arc Length O (Nom)	5.0 mm

Operating and Electrical	
Power Consumption	200 W
Lamp Current (Nom)	3.3 A

Controls and Dimming	
Dimmable	Yes


Product Data	
Order product name	MSR 200 HR 1CT/4
Full product name	MSR 200 HR 1CT/4
Full product code	871869641604400
Order code	928097905115
Material Nr. (12NC)	928097905115
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696416044
Numerator - Packs per outer box	4

MSR Hot Restrike

EAN/UPC - Case


8718696416051

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR 200	20 mm	5.0	38 mm	40 mm	39	80 mm	24 mm	23.5	23 mm
HR 1CT/4		mm			mm			mm	

Photometric data



Spectral Power Distribution Colour - MSR 200 HR 1CT/4

