



MSR Gold™ SA Double Ended

MSR Gold 1510 SA/1 DE 1CT/4

To optimize the total lifetime of the double ended MSR Gold™ SA Double Ended lamps, the caps are plated with gold. This provides superior heat protection and thereby minimizes premature failure of the lamp and lamp holder, as well as ensuring extended consistent performance. In addition, the highly innovative P3 technology, developed by Philips, allows the lamp to be used at higher temperatures, which further extends service life and consistency of high-quality light output.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Arc Length O (Nom)	
Cap-Base	SFC10-4 [SFC10-4]	7 mm	
Operating Position	UNIVERSAL [Any or Universal (U)]	Operating and Electrical	
Life to 50% Failures (Nom)	750 hour(s)	Power Consumption	1,510 W
Light Technical		Lamp Current (Nom)	13.4 A
Color Code	- [Not Specified]	Controls and Dimming	
Luminous Flux	141,000 lm	Dimmable	Yes
Chromaticity Coordinate X (Nom)	330	Product Data	
Chromaticity Coordinate Y (Nom)	338	Order product name	MSR Gold 1510 SA/1 DE 1CT/4
Correlated Color Temperature (Nom)	5600 K	Full product name	MSR Gold 1510 SA/1 DE 1CT/4
Luminous Efficacy (rated) (Nom)	91 lm/W	Full product code	692059027773300
Color rendering index (CRI)	90		

MSR Gold™ SA Double Ended

Order code	928410005123
Material Nr. (12NC)	928410005123
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6920590277733


Numerator - Packs per outer box	4
EAN/UPC - Case	6920590277740

Dimensional drawing



Product	A (max)	A (min)	A	C (max)	D (max)	O
MSR Gold 1510 SA/1 DE 1CT/4	115.2 mm	114.4 mm	114.8 mm	136 mm	23 mm	7 mm

Photometric data



Spectral Power Distribution Colour - MSR Gold 1510 SA/1 DE 1CT/4

