



MSD Platinum (Touring/Stage)

MSD Platinum 200 Flex 1CT/8

The MSD Platinum lamps open up new levels of creative freedom in entertainment lighting, with powerful, compact and brilliantly intense light. Their compact, lightweight design provides the freedom to create smaller, lighter luminaires – for use at any location on stage. And their short arc, high color temperature and innovative reflector produce a sparkling, high beam intensity for outstanding color reproduction. They also offer long and reliable lifetime, high efficacy and fast replacement times. It all adds up to an intensely exciting creative experience.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	- [-]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	2,000 hour(s)

Light Technical	
Color Code	2
Luminous Flux	14,000 lm
Chromaticity Coordinate X (Nom)	0.300
Chromaticity Coordinate Y (Nom)	0.305
Correlated Color Temperature (Nom)	7800 K
Arc Length O (Nom)	0.8 mm

Operating and Electrical	
Power Consumption	240 W



Controls and Dimming	
Dimmable	Yes

Product Data	
Order product name	MSD Platinum 200 Flex 1CT/8
Full product name	MSD Platinum 200 Flex 1CT/8
Full product code	871869680813900
Order code	928495705314
Material Nr. (12NC)	928495705314
Numerator - Quantity Per Pack	1

MSD Platinum (Touring/Stage)


EAN/UPC - Product/Case	8718696808139
Numerator - Packs per outer box	8
EAN/UPC - Case	8718696808146

Dimensional drawing



Product	D (max)	O	C (max)	T
MSD Platinum 200 Flex 1CT/8	56.5 mm	0.8 mm	60 mm	7 mm

Photometric data



Spectral Power Distribution Colour - MSD Platinum 200 Flex 1CT/8

