



CorePro LEDcapsule MV

CorePro LEDcapsuleMV 2.5-25W 827 G9

The LED specialties deliver a high quality light to make themselves to be a true replacement of halogen specialty lamp (such as G9 and R7S). It is particularly suit for task lighting in hotel and restaurants, and ideal for decorative and ambient application. LEDspecialty products deliver huge energy saving and minimize maintenance costs, without any compromise on light quality.

Product data

General Information	
Cap-Base	G9 [G9]
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	204 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	81.6 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 Hz
Input Frequency	50 Hz


Power Consumption	2.5 W
Lamp Current (Nom)	29 mA
Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	Capsule
Approval and Application	
Energy Consumption kWh/1000 h	3 kWh
Product Data	
Order product name	CorePro LEDcapsuleMV 2.5-25W 827 G9
Full product name	CorePro LEDcapsuleMV 2.5-25W 827 G9

CorePro LEDcapsule MV

Full product code	871869641920500
Order code	929001133402
Material Nr. (12NC)	929001133402
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696419205


Numerator - Packs per outer box	12
EAN/UPC - Case	8718696419212

Dimensional drawing



Product	D	C
CorePro LEDcapsuleMV 2.5-25W 827 G9	18 mm	53 mm

Photometric data



Light Distribution Diagram - CorePro LEDcapsuleMV 2.5-25W 827 G9

Spectral Power Distribution Colour - CorePro LEDcapsuleMV 2.5-25W 827 G9

